



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	485203835	Response Date	2014-04-04	Contact Email	cc.wu@tycoelectronics.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	770971-2	Amount	3774.521	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true																																	
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	770603-2				5.0	132.21	mg																										
Material	2	Tin-Lead Plate				5.0	1.063	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	5.0	0.007441	mg																										
Substance	3	Tin	Supplier	7440-31-5	92.3	5.0	0.98115	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	5.0	0.07441	mg																										
Material	2	Nickel Plate				5.0	0.691	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	5.0	0.001382	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	6.91E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	0.68893	mg																										
Material	2	Brass				5.0	130.2	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	5.0	0.09114	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	5.0	93.093	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	5.0	0.001302	mg																										
Substance	3	Zinc	Supplier	7440-66-6	27.9975	5.0	36.45274	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	5.0	0.0651	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	5.0	0.001302	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	5.0	0.0651	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.1302	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	5.0	0.01302	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.01302	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.01302	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	6.51E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	5.0	0.2604	mg																										
Material	2	Gold Plate				5.0	0.256	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	5.0	0.00256	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.0	5.0	0.25344	mg																										
Sub-Item	1	770604-2				5.0	182.6942	mg																										
Material	2	Tin-Lead Plate				5.0	2.0533	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	5.0	0.0143731	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	5.0	1.8952	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	5.0	0.14373	mg	
Material	2	Nickel Plate				5.0	1.085	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	5.0	0.00217	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	0.001085	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	1.08175	mg	
Material	2	Brass				5.0	179.3	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	5.0	0.12551	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	5.0	128.1995	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	5.0	0.001793	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	5.0	50.19952	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	5.0	0.08965	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	5.0	0.001793	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	5.0	0.08965	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.1793	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	5.0	0.01793	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.01793	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.01793	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	8.965E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	5.0	0.3586	mg	
Material	2	Gold Plate				5.0	0.2559	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	5.0	0.002559	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	5.0	0.25334	mg	
Sub-Item	1	770958-1				1.0	2200.0	mg	
Material	2	PA				1.0	2200.0	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	7.1764	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	10.2014	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.0066	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	20.7922	mg	
Substance	3	Benzenepropionamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	8.8088	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.0726	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.55	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	4.4264	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	4.1822	mg	
Substance	3	1,3,5-Triazine-2,4,6(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	199.5774	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	1944.206	mg	