



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Rohde, Daniel F.	Contact Title	Prod Sustaining Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-05-02	Contact Email	daniel.rohde@te.com																													
Contact Phone Number		+1-717-986-3211																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	2-36161-3	Amount	2250.82882078	Version	-	Identity																												
Manufacturer Item Name	TERMINAL,PID G R IR 12 10	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	SLEEVE ASSEMBLY 12 IR				1.0	860.36882078	mg																										
Material	2	PA66				1.0	196.04853257	mg																										
Substance	3	Copper	Supplier	7440-50-8	0.02	1.0	0.03920971	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	2.15653	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.78	1.0	193.65674	mg																										
Substance	3	Bromine	Supplier	7726-95-6	0.1	1.0	0.19605	mg																										
Material	2	Copper				1.0	662.0	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.331	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.662	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00662	mg																										
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	659.99745	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00662	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0662	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0662	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.1324	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.662	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00331	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0662	mg																										
Material	2	Nickel Plate				1.0	0.34	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	6.8E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.4E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.33898	mg																										
Material	2	COLORANT				1.0	1.98028821	mg																										
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	2.0	1.0	0.03960576	mg																										
Substance	3	Poly[imino(1-oxo-1,6-hexanediyl)]	Supplier	25038-54-4	95.5	1.0	1.89118	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	0.00990144	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	0.03960576	mg	
Sub-Item	1	TERMINAL,BRAZED R 12-10 10				1.0	1390.46	mg	
Material	2	Tin Plate				1.0	11.0	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	10.945	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.044	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.011	mg	
Material	2	Copper				1.0	1369.03	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.68452	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.36903	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0136903	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	1364.88868	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0136903	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1369	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1369	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.27381	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.36903	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00684515	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1369	mg	
Material	2	Brazing Filler				1.0	10.43	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.7	1.0	0.69881	mg	
Substance	3	Copper	Supplier	7440-50-8	87.05	1.0	9.07932	mg	
Substance	3	Silver	Supplier	7440-22-4	6.25	1.0	0.65188	mg	