



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Mgr Environmental Engineering		
Company Unique ID	TE Connectivity	Response Date	2015-02-12	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	826629-8	Amount	0.532496	Version	-	Identity			
Manufacturer Item Name	AMPMODU II HEADER	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOD II SQ0.63 CONTACT PIN,BLDR,PD NI				8.0	0.043762	g	
Material	2	Brass Wire				8.0	0.043	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	8.0	3.01E-5	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	8.0	0.030745	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	8.0	4.3E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	8.0	0.01203893	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	8.0	2.15E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	8.0	4.3E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	8.0	2.15E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	8.0	4.3E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	8.0	4.3E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	8.0	4.3E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	8.0	4.3E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	8.0	2.15E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	8.0	8.6E-5	g	
Material	2	Tin Plate				8.0	2.5E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	8.0	2.4975E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.9001	8.0	2.4975E-4	g	
Material	2	Nickel Plate				8.0	4.3E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	8.0	8.6E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	8.0	4.3E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	8.0	4.2871E-4	g	
Material	2	Palladium-Nickel Plate				8.0	8.2E-5	g	
Substance	3	Palladium	Supplier	7440-05-3	80.0	8.0	6.56E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	20.0	8.0	1.64E-5	g	
Sub-Item	1	MOD2STGH,1 RHG50P,GN				0.16	1.14	g	
Material	2	Polyester Compound				0.16	1.14	g	

Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.0	0.16	0.627	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	0.16	0.342	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	5.0	0.16	0.057	g	
Substance	3	Antimony oxide (Sb ₂ O ₃)	Supplier	1309-64-4	5.0	0.16	0.057	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.0	0.16	0.057	g	