



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	485203835	Response Date	2013-09-17	Contact Email	cc.wu@tycoelectronics.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1650162-2	Amount	160.894203	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s) - true																																	
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Nickel Plate				1.0	0.599725	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.00119945	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.9972E-4	mg																										
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	0.59793	mg																										
Material	1	Brass				1.0	160.0	mg																										
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0016	mg																										
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.016	mg																										
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.16	mg																										
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.016	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.032	mg																										
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0016	mg																										
Substance	2	Iron	Supplier	7439-89-6	0.35	1.0	0.56	mg																										
Substance	2	Zinc	Supplier	7440-66-6	32.7475	1.0	52.396	mg																										
Substance	2	Copper	Supplier	7440-50-8	63.0	1.0	100.8	mg																										
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	8.0E-4	mg																										
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.016	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	5.92	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight																									
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	0.08	mg																										
Material	1	Gold Plate				1.0	0.294478	mg																										
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.29359	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	8.8343E-4	mg																										