



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-05-07	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	215307-6	Amount	888.8185	Version	-	Identity																												
Manufacturer Item Name	2X6P HV100 REC CON. TE, 7.0MM	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	HV100 CNT U-ED, AU PLATED- NI UNDERPLATE				12.0	33.574	mg																										
Material	2	Nickel Plate				12.0	0.048	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	9.6E-5	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	4.8E-5	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	0.047856	mg																										
Material	2	Gold Plate				12.0	0.042	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.0	12.0	0.04158	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	12.0	4.2E-4	mg																										
Material	2	Phos Bronze				12.0	33.28	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6835	12.0	31.51067	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	12.0	0.006656	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	12.0	0.003328	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	12.0	1.4976	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	12.0	0.004992	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	12.0	0.03328	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	0.003328	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	3.328E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	12.0	0.09984	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	12.0	0.03328	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	0.03328	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	12.0	0.003328	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	0.01664	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	12.0	0.03328	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	1.664E-4	mg																										
Material	2	Tin Plate				12.0	0.201	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	12.0	2.008E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	12.0	0.2008	mg																										
Material	2	Gold Plate				12.0	0.0030	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	12.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	12.0	0.002991	mg	
Sub-Item	1	2X36P HV100 HSG 7.0MM, TAPED				0.1667	2915.0	mg	
Material	2	Polyester Compound				0.1667	2915.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	50.0	0.1667	1457.5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.0	0.1667	145.75	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	10.0	0.1667	291.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	15.0	0.1667	437.25	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	0.1667	583.0	mg	