



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER																											
Company Unique ID	-	Response Date	2013-07-18	Contact Email	cc.wu@te.com																													
Contact Phone Number		(86)21-33259321																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	284392-8	Amount	6541.75	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s) - true																																	
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-1212	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Plastic housing				1.0	1697.5	mg																										
Substance	2	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	100.0	1.0	1697.5	mg																										
Material	1	Terminals Ni plating				1.0	9.7672	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	9.7672	mg																										
Material	1	Screws Ni plating				1.0	8.44	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	8.44	mg																										
Material	1	Terminals Sn plating				1.0	23.9128	mg																										
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	23.9128	mg																										
Material	1	Rising clamps				1.0	2389.79	mg																										
Substance	2	Copper	Supplier	7440-50-8	59.0	1.0	1409.9761	mg																										
Substance	2	Zinc	Supplier	7440-66-6	39.0	1.0	932.0181	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	2.0	1.0	47.7958	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight																									
Material	1	Rising clamps plating				1.0	9.56	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	9.56	mg																										
Material	1	Terminals				1.0	731.6	mg																										
Substance	2	Zinc	Supplier	7440-66-6	29.5	1.0	215.822	mg																										
Substance	2	Tin	Supplier	7440-31-5	0.1	1.0	0.7316	mg																										
Substance	2	Copper	Supplier	7440-50-8	70.0	1.0	512.12	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.7316	mg																										
Substance	2	Nickel	Nickel	7440-02-0	0.3	1.0	2.1948	mg																										
Material	1	Screws				1.0	1671.18	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.32	1.0	5.34778	mg																										
Substance	2	Copper	Supplier	7440-50-8	93.29	1.0	1559.04382	mg																										
Substance	2	Zinc	Supplier	7440-66-6	0.11	1.0	1.8383	mg																										
Substance	2	Tin	Supplier	7440-31-5	6.27	1.0	104.78299	mg																										
Substance	2	Nickel	Nickel	7440-02-0	0.01	1.0	0.16712	mg																										