



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	485203835	Response Date	2014-03-20	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	3-5435640-5	Amount	170680.29678	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	382540-7				5.0	13.04788	mg																										
Material	2	Tin Plate				5.0	0.124	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	5.0	1.2388E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	5.0	0.12388	mg																										
Material	2	Gold Plate				5.0	0.00688	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	5.0	0.00685936	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	5.0	2.064E-5	mg																										
Material	2	Beryllium Copper				5.0	12.537	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.0012537	mg																										
Substance	3	Copper	Supplier	7440-50-8	96.9485	5.0	12.15443	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	0.0025074	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.0012537	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.6	5.0	0.075222	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	5.0	0.0012537	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.012537	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	5.0	1.2537E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	0.012537	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	6.2685E-5	mg																										
Substance	3	Nickel	Nickel	7440-02-0	2.2	5.0	0.27581	mg																										
Material	2	Nickel Plate				5.0	0.38	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	5.0	7.6E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	3.8E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	0.37886	mg																										
Sub-Item	1	435506-3				1.0	460.0	mg																										
Material	2	PBT-GF30-FR(17)				1.0	460.0	mg																										
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	234.6	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	36.8	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	133.4	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	18.4	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	36.8	mg	
Sub-Item	1	437002-3				1.0	242.47	mg	
Material	2	PBT-GF30FR(17)				1.0	242.47	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	72.741	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	80.0151	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	2.4247	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	2.4247	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	12.1235	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	72.741	mg	
Sub-Item	1	997810-1				1.0	169643.54638	mg	
Sub-Item	1	4-435234-1				4.0	51.0	mg	
Material	2	PBT				4.0	51.0	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	4.0	0.102	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	4.0	2.55	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	4.0	0.051	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	4.0	4.08	mg	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	4.0	0.051	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	4.0	0.255	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	4.0	0.051	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	4.0	15.3	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	4.0	0.255	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	4.0	2.55	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	4.0	1.02	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	4.0	0.051	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	4.0	24.684	mg	
Sub-Item	1	382541-8				5.0	13.0082	mg	
Material	2	Tin Plate				5.0	0.124	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	5.0	1.2388E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	5.0	0.12388	mg	
Material	2	Gold Plate				5.0	0.0032	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	5.0	0.0031904	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	5.0	1.0E-5	mg	
Material	2	Beryllium Copper				5.0	12.5	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.00125	mg	
Substance	3	Copper	Supplier	7440-50-8	96.9485	5.0	12.11856	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	0.0025	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.00125	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	5.0	0.075	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	5.0	0.00125	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.0125	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	5.0	1.25E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	0.0125	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	6.25E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	2.2	5.0	0.275	mg	
Material	2	Nickel Plate				5.0	0.381	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	5.0	7.62E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	3.81E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	0.37986	mg	