



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																
Supplier Information																									
Company Name	TE Connectivity	Request Document ID		Contact Name	PIC	Contact Title	PS																		
Company Unique ID	TE	Response Date	2014-05-28	Contact Email	pic.us@te.com																				
Contact Phone Number	800-522-6752																								
Legal Statement																									
Supplier Acceptance	true																								
Legal Statement																									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																									
Product																									
Manufacturer Item number	1625854-1	Amount	0.02154451	Version	-	Identity																			
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority																			
Date		UOM	Each																						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																								
EUREACH-0613	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true																								
Product Disclosure																									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																
Material	1	Stainless steel				1.0	0.02099958	g																	
Substance	2	Iron	Supplier	7439-89-6	72.0	1.0	0.0151197	g	N/A																
Substance	2	Chromium	Supplier	7440-47-3	18.0	1.0	0.00377993	g	N/A																
Substance	2	Nickel	Nickel	7440-02-0	10.0	1.0	0.00209996	g	N/A																
Material	1	plating				1.0	5.2334E-4	g																	
Substance	2	Tin	Supplier	7440-31-5	2.3121	1.0	1.210018E-5	g	N/A																
Substance	2	Copper	Supplier	7440-50-8	97.6879	1.0	5.1124E-4	g	N/A																
Material	1	Under electrode				1.0	2.15852E-5	g																	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	2.15852E-5	g	N/A																