



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Manager Environmental Engineering																											
Company Unique ID	485203835	Response Date	2014-05-05	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	435640-5	Amount	1860.4669	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true																																	
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	4-435234-1				8.0	51.0	mg																										
Material	2	PBT				8.0	51.0	mg																										
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	8.0	0.102	mg																										
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	8.0	2.55	mg																										
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	8.0	0.051	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	8.0	4.08	mg																										
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	8.0	0.051	mg																										
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	8.0	0.255	mg																										
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	8.0	0.051	mg																										
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	8.0	15.3	mg																										
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	8.0	0.255	mg																										

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	8.0	2.55	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	8.0	1.02	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	8.0	0.051	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	8.0	24.684	mg	
Sub-Item	1	437002-7				1.0	538.0	mg	
Material	2	PBT-GF30FR(17)				1.0	538.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	161.4	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	177.54	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	5.38	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	5.38	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	26.9	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	161.4	mg	
Sub-Item	1	382540-1				9.0	9.1669	mg	
Material	2	Nickel Plate				9.0	0.25	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	5.0E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	2.5E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	9.0	0.24925	mg	
Material	2	Beryllium Copper				9.0	8.34	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	9.0	8.34E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	96.9485	9.0	8.0855	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	9.0	0.001668	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	9.0	8.34E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	9.0	0.05004	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	9.0	8.34E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	9.0	0.00834	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	9.0	8.34E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	0.00834	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	9.0	4.17E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	2.2	9.0	0.18348	mg	
Material	2	Tin-Lead Plate				9.0	0.57	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	9.0	0.52611	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	9.0	0.00399	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	9.0	0.0399	mg	
Material	2	Gold Plate				9.0	0.0069	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	9.0	0.0068793	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	9.0	2.07E-5	mg	
Sub-Item	1	382541-1				9.0	9.3532	mg	
Material	2	Nickel Plate				9.0	0.26	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	5.2E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	2.6E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	9.0	0.25922	mg	
Material	2	Beryllium Copper				9.0	8.51	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	9.0	8.51E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	96.9485	9.0	8.25032	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	9.0	0.001702	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	9.0	8.51E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	9.0	0.05106	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	9.0	8.51E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	9.0	0.00851	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	9.0	8.51E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	0.00851	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	9.0	4.255E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	2.2	9.0	0.18722	mg	
Material	2	Tin-Lead Plate				9.0	0.58	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	9.0	0.53534	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	9.0	0.00406	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	9.0	0.0406	mg	
Material	2	Gold Plate				9.0	0.0032	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	9.0	0.0031904	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	9.0	1.0E-5	mg	
Sub-Item	1	435506-7				1.0	747.786	mg	
Material	2	PBT-GF30-FR(17)				1.0	747.786	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	381.37086	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	59.82288	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	216.85794	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	29.91144	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	59.82288	mg	