



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2014-09-09	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1625854-2	Amount	13.9237	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Nickel Plating				1.0	0.0122	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.0122	mg	
Material	1	Stainless steel				1.0	13.6164	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.03	1.0	0.00408492	mg	
Substance	2	Iron	Supplier	7439-89-6	70.925	1.0	9.65743	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.045	1.0	0.00612738	mg	
Substance	2	Silicon	Supplier	7440-21-3	1.0	1.0	0.13616	mg	
Substance	2	Manganese	Supplier	7439-96-5	2.0	1.0	0.27233	mg	
Substance	2	Chromium	Supplier	7440-47-3	18.0	1.0	2.45095	mg	
Substance	2	Nickel	Nickel	7440-02-0	8.0	1.0	1.08931	mg	
Material	1	Tin Copper Plating				1.0	0.2951	mg	
Substance	2	Copper	Supplier	7440-50-8	2.0	1.0	0.005902	mg	
Substance	2	Tin	Supplier	7440-31-5	98.0	1.0	0.2892	mg	