



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Mgr Environmental Engineering		
Company Unique ID	-	Response Date	2014-07-21	Contact Email	jrpenica@te.com				
Contact Phone Number	1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	9-1393239-5	Amount	13013.722	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	10.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1936827-2				1.0	330.0	mg	
Material	2	Copper				1.0	104.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.052	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.104	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00104	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	103.6854	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00104	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0104	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0104	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0208	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.104	mg	
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	1.0	5.2E-4	mg	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.01	1.0	0.0104	mg	
Material	2	AgNi/10/B/- /AgNi10P/				1.0	171.0	mg	
Substance	3	Silver	Supplier	7440-22-4	90.0	1.0	153.9	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	17.1	mg	
Material	2	Copper Alloy				1.0	55.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0275	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	1.0	0.55	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	1.0	0.66	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.055	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7635	1.0	51.01992	mg	

Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	0.033	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.5E-4	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	1.0	0.165	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	1.0	0.055	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	1.0	0.11	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0055	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0055	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	1.0	2.31	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00275	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.75E-4	mg	
Sub-Item	1	1936803-3				1.0	4002.0	mg	
Material	2	Copper Plate				1.0	32.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.032	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	31.968	mg	
Material	2	100-2220				1.0	3952.0	mg	
Substance	3	Vanadium	Supplier	7440-62-2	0.0070	1.0	0.27664	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.15	1.0	5.928	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.3952	mg	
Substance	3	Titanium	Supplier	7440-32-6	0.0070	1.0	0.27664	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.36	1.0	14.2272	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.09	1.0	3.5568	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.022	1.0	0.86944	mg	
Substance	3	Copper	Supplier	7440-50-8	0.08	1.0	3.1616	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.3952	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.01	1.0	0.3952	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	2.3712	mg	
Substance	3	Iron	Supplier	7439-89-6	98.8885	1.0	3908.07352	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.022	1.0	0.86944	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.952	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.03952	mg	
Substance	3	Nitrogen	Supplier	7727-37-9	0.0070	1.0	0.27664	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.07	1.0	2.7664	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01976	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.952	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.1976	mg	
Material	2	Nickel Plate				1.0	18.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.036	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.018	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	17.946	mg	
Sub-Item	1	1936826-1				1.0	684.0	mg	
Material	2	Copper				1.0	524.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.262	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.524	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00524	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	522.4149	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00524	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0524	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0524	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.1048	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.524	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00262	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0524	mg	
Material	2	AgNi10/B/-/AgNi10P				1.0	160.0	mg	
Substance	3	Silver	Supplier	7440-22-4	90.0	1.0	144.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	16.0	mg	
Sub-Item	1	1936812-2				1.0	219.0	mg	
Material	2	PBT-GF30 FR (17)				1.0	219.0	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	13.0	1.0	28.47	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	51.7	1.0	113.223	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.657	mg	
Substance	3	Fluorine	Supplier	7782-41-4	1.0	1.0	2.19	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	65.7	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	8.76	mg	
Sub-Item	1	1936804-3				1.0	824.0	mg	
Material	2	Copper Plate				1.0	12.7	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0127	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	12.6873	mg	
Material	2	100-2220				1.0	804.0	mg	
Substance	3	Vanadium	Supplier	7440-62-2	0.0070	1.0	0.05628	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.15	1.0	1.206	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0804	mg	
Substance	3	Titanium	Supplier	7440-32-6	0.0070	1.0	0.05628	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.36	1.0	2.8944	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.09	1.0	0.7236	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.022	1.0	0.17688	mg	
Substance	3	Copper	Supplier	7440-50-8	0.08	1.0	0.6432	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0804	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.01	1.0	0.0804	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	0.4824	mg	
Substance	3	Iron	Supplier	7439-89-6	98.8885	1.0	795.06354	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.022	1.0	0.17688	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.804	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00804	mg	
Substance	3	Nitrogen	Supplier	7727-37-9	0.0070	1.0	0.05628	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.07	1.0	0.5628	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00402	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.804	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0402	mg	
Material	2	Nickel Plate				1.0	7.3	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0146	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0073	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	7.2781	mg	
Sub-Item	1	1936811-4				1.0	1700.0	mg	
Material	2	VESTODUR X7212 NATURAL, A				1.0	1700.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.0	1.0	102.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	41.0	1.0	697.0	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	8.0	1.0	136.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	765.0	mg	
Sub-Item	1	1936826-5				1.0	684.0	mg	
Material	2	Copper				1.0	524.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.262	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.524	mg	

Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00524	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	522.4149	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00524	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0524	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0524	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.1048	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.524	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00262	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0524	mg	
Material	2	AgNi/10/B/-/AgNi10P				1.0	160.0	mg	
Substance	3	Silver	Supplier	7440-22-4	90.0	1.0	144.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	16.0	mg	
Sub-Item	1	1915650-1				1.0	139.0	mg	
Material	2	ADHESIVE				1.0	139.0	mg	
Substance	3	C.I. Pigment Yellow 42	Supplier	51274-00-1	0.2	1.0	0.278	mg	
Substance	3	Siloxanes and Silicones, di-Me, reaction products with silica	Supplier	67762-90-7	1.3	1.0	1.807	mg	
Substance	3	Oxirane, 2-[[3-(trimethoxysilyl)propoxy]methyl]-	Supplier	2530-83-8	0.2	1.0	0.278	mg	
Substance	3	1,3-Propanediol, 2-ethyl-2-(hydroxymethyl)-, polymer with (chloromethyl)oxirane	Supplier	30499-70-8	7.0	1.0	9.73	mg	
Substance	3	Phenol, polymer with formaldehyde, glycidyl ether	Supplier	28064-14-4	6.0	1.0	8.34	mg	
Substance	3	Ajicure PN 23	Supplier	134091-76-2	13.9	1.0	19.321	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane	Supplier	25068-38-6	59.4	1.0	82.566	mg	
Substance	3	Limestone	Supplier	1317-65-3	12.0	1.0	16.68	mg	
Sub-Item	1	1816101-3				1.0	11.6	mg	
Material	2	Beryllium Copper				1.0	11.6	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00116	mg	
Substance	3	Copper	Supplier	7440-50-8	96.9485	1.0	11.24603	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.00232	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00116	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	1.0	0.0696	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00116	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0116	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	1.16E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0116	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	5.8E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	2.2	1.0	0.2552	mg	
Sub-Item	1	1936810-1				1.0	1131.122	mg	
Material	2	Polyester Compound				1.0	1131.122	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	12.5	1.0	141.39025	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	11.0	1.0	124.42342	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol]	Supplier	25971-63-5	60.5	1.0	684.32881	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	16.0	1.0	180.97952	mg	
Sub-Item	1	5-2054002-4				1.0	3289.0	mg	

Material	2	VESTODUR X7212 NATURAL, A				1.0	297.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.0	1.0	17.82	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	41.0	1.0	121.77	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	8.0	1.0	23.76	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	133.65	mg	
Material	2	Copper				1.0	2960.0	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.296	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0296	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.296	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.592	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	2951.046	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.96	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0296	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.296	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.96	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.48	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0148	mg	
Material	2	Phos Bronze				1.0	32.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.112	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.032	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.0048	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.032	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0064	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	3.2E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0032	mg	
Substance	3	Tin	Supplier	7440-31-5	7.0	1.0	2.24	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.096	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.0032	mg	
Substance	3	Copper	Supplier	7440-50-8	91.9385	1.0	29.42032	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.032	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.016	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0016	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.6E-4	mg	