



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-06-22	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	787685-1	Amount	14486.9044974	Version	-	Identity			
Manufacturer Item Name	37 RCPT SP/FMS (RET SL)	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	37 SPFMS RCPT HSG				1.0	5892.2	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	5892.2	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	29.461	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	2062.27	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	11.7844	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	11.7844	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	176.766	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	117.844	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	58.922	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	29.461	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	58.922	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	2156.5452	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	29.461	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	1060.596	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	29.461	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	58.922	mg	
Sub-Item	1	SHELL,FRT,R CPT,SZ4,PLATED				1.0	4133.486855	mg	
Material	2	Carbon Steel				1.0	3919.4	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	1.9597	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.39194	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.78388	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	5.8791	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.9194	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.039194	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.39194	mg	
Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	3838.4056	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.9194	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	29.3955	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	1.37179	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	23.5164	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	3.13552	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.019597	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.9194	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.9597	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.39194	mg	
Material	2	Tin Plate				1.0	133.00715	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.13301	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.53203	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	132.34211	mg	
Material	2	Copper Plate				1.0	81.079705	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0810797	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	80.99863	mg	
Sub-Item	1	20 DF SCKT/26 RD,AU30-SP				37.0	67.2394152	mg	
Material	2	Phos Bronze				37.0	65.7	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	37.0	62.20706	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	37.0	0.01314	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	37.0	0.00657	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	37.0	2.9565	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	37.0	0.009855	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	37.0	0.0657	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	37.0	0.00657	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	37.0	6.57E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	37.0	0.1971	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	37.0	0.0657	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	37.0	0.0657	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	37.0	0.00657	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	37.0	0.03285	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	37.0	0.0657	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	37.0	3.285E-4	mg	
Material	2	Nickel Plate				37.0	1.07925	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	37.0	0.0021585	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	37.0	0.00107925	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	37.0	1.07601	mg	

Material	2	Gold Plate				37.0	0.0301112	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	37.0	9.03336E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	37.0	0.03002087	mg	
Material	2	Gold Plate				37.0	0.040644	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	37.0	0.04052207	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	37.0	1.2193E-4	mg	
Material	2	Tin-Lead Plate				37.0	0.38941	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	37.0	0.0272587	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	37.0	0.35943	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	37.0	0.00272587	mg	
Sub-Item	1	SCREWLOCK-BOARDLOCK (PLTD)				2.0	986.67964	mg	
Material	2	Nickel Plate				2.0	7.29224	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.01458448	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00729224	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	7.27036	mg	
Material	2	Brass				2.0	968.3	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.009683	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.09683	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.9683	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.09683	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.19366	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.009683	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	2.0	3.38905	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	2.0	317.09404	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	2.0	610.029	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.0048415	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.09683	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	2.0	35.8271	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.48415	mg	
Material	2	Tin-Lead Plate				2.0	10.8687	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	2.0	10.03181	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	2.0	0.0760809	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	2.0	0.76081	mg	
Material	2	Copper Plate				2.0	0.2187	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.187E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	0.21848	mg	