



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-04-17	Contact Email	jp.kuntz@te.com				
Contact Phone Number	717-986-5932								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	8-215570-0	Amount	696.40632	Version	-	Identity			
Manufacturer Item Name	MICRO-MATCH PBC.10P	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MICRO-MATCH M COVER				1.0	104.0	mg	
Material	2	POLYESTER PBT				1.0	104.0	mg	
Substance	3	1,4-Benzenedicarb oxylc acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.0	1.0	56.16	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.0	1.0	19.76	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	4.0	1.0	4.16	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	4.16	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromoph enyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	19.0	1.0	19.76	mg	
Sub-Item	1	MICRO-MATCH P.B.HSG				1.0	288.44	mg	
Material	2	POLYESTER PBT				1.0	288.44	mg	
Substance	3	1,4-Benzenedicarb oxylc acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.0	1.0	155.7576	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.0	1.0	54.8036	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	4.0	1.0	11.5376	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	11.5376	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromoph enyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	19.0	1.0	54.8036	mg	

Sub-Item	1	MICRO MATCH PB CONT				10.0	30.396632	mg	
Material	2	Phos Bronze				10.0	30.1	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	10.0	28.49973	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.00602	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.00301	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	1.3545	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.004515	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.00301	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.0301	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	3.01E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.0903	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	0.0301	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.0301	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.00301	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.01505	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.0301	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	1.505E-4	mg	
Material	2	Tin Plate				10.0	0.1825	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	1.8232E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.18232	mg	
Material	2	Nickel Plate				10.0	0.114132	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	2.2826E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	1.1413E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.11379	mg	