



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Rohde, Daniel F.	Contact Title	Prod Sustaining Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-05-02	Contact Email	daniel.rohde@te.com				
Contact Phone Number	+1-717-986-3211								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	35634	Amount	4319.605059	Version	-	Identity			
Manufacturer Item Name	TERMINAL,PID G R 16-14HD 6	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	TERMINAL,BU DG R 16-14HD 6				1.0	1378.485499	mg	
Material	2	Tin Plate				1.0	9.007838	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	8.9628	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.03603135	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00900784	mg	
Material	2	Copper				1.0	1369.477661	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.68474	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.36948	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01369478	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	1365.33499	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01369478	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.13695	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.13695	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.2739	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.36948	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00684739	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.13695	mg	
Sub-Item	1	SLEEVE ASSEMBLY 16-14 HD				1.0	2941.11956	mg	
Material	2	PA66				1.0	2210.3560332	mg	
Substance	3	Copper	Supplier	7440-50-8	0.02	1.0	0.44207	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	24.31392	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	98.78	1.0	2183.38969	mg	
Substance	3	Bromine	Supplier	7726-95-6	0.1	1.0	2.21036	mg	
Material	2	Tin Plate				1.0	9.762	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	9.71319	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.039048	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.009762	mg	
Material	2	COLORANT				1.0	68.3615268	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	2.0	1.0	1.36723	mg	
Substance	3	Poly[[imino(1-oxo-1,6-hexanediy)]]	Supplier	25038-54-4	95.5	1.0	65.28526	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	0.34181	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	1.36723	mg	
Material	2	Copper				1.0	652.64	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.32632	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.65264	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0065264	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	650.66576	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0065264	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.065264	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.065264	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.13053	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.65264	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0032632	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.065264	mg	