



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-06-30	Contact Email	jp.kuntz@te.com																													
Contact Phone Number		717-986-5932																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1437575-3	Amount	80.0	Version	-	Identity																												
Manufacturer Item Name	MLL1300S=SP3 T RA SMT SLIDE	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	COVER_NiAg				1.0	33.0	mg																										
Substance	2	Nickel	Nickel	7440-02-0	17.0	1.0	5.61	mg																										
Substance	2	Zinc	Supplier	7440-66-6	17.545	1.0	5.78985	mg																										
Substance	2	Copper	Supplier	7440-50-8	65.455	1.0	21.60015	mg																										
Material	1	CONTACT PLATE_Cu Alloy				1.0	3.0	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0030	1.0	9.0E-5	mg																										
Substance	2	Zinc	Supplier	7440-66-6	0.01	1.0	3.0E-4	mg																										
Substance	2	Chromium	Supplier	7440-47-3	0.0050	1.0	1.5E-4	mg																										
Substance	2	Cobalt	Supplier	7440-48-4	0.22	1.0	0.0066	mg																										
Substance	2	Aluminum	Supplier	7429-90-5	0.018	1.0	5.4E-4	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.03	1.0	9.0E-4	mg																										
Substance	2	Silicon	Supplier	7440-21-3	0.04	1.0	0.0012	mg																										
Substance	2	Beryllium	Supplier	7440-41-7	1.925	1.0	0.05775	mg																										
Substance	2	Copper	Supplier	7440-50-8	97.739	1.0	2.93217	mg																										
Substance	2	Nickel	Nickel	7440-02-0	0.01	1.0	3.0E-4	mg																										
Material	1	TERMINAL_Ag plating				1.0	2.0	mg																										
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	2.0	mg																										
Material	1	FRAME_LCP				1.0	22.0	mg																										
Substance	2	Carbon black	Supplier	1333-86-4	5.0	1.0	1.1	mg																										
Substance	2	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,4-benzenediol, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	96892-06-7	65.0	1.0	14.3	mg																										
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	6.6	mg																										
Material	1	TERMINAL_Cu Alloy				1.0	10.0	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.0090	1.0	9.0E-4	mg																										
Substance	2	Zinc	Supplier	7440-66-6	34.382	1.0	3.4382	mg																										
Substance	2	Copper	Supplier	7440-50-8	65.607	1.0	6.5607	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0020	1.0	2.0E-4	mg																										

Material	1	SLIDER_PA46				1.0	6.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1.8	mg	
Substance	2	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	70.0	1.0	4.2	mg	
Material	1	SPRING PLATE_Stainless steel				1.0	1.0	mg	
Substance	2	Manganese	Supplier	7439-96-5	1.238	1.0	0.01238	mg	
Substance	2	Iron	Supplier	7439-89-6	74.018	1.0	0.74018	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.0050	1.0	5.0E-5	mg	
Substance	2	Carbon	Supplier	7440-44-0	0.094	1.0	9.4E-4	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.581	1.0	0.00581	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.023	1.0	2.3E-4	mg	
Substance	2	Chromium	Supplier	7440-47-3	17.17	1.0	0.1717	mg	
Substance	2	Nickel	Nickel	7440-02-0	6.871	1.0	0.06871	mg	
Material	1	CONTACT PLATE_Ag plating				1.0	1.0	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	1.0	mg	
Material	1	TERMINAL_Ni plating				1.0	2.0	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	2.0	mg	