



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	M. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2014-11-07	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1571983-0	Amount	696.0	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	M plate				1.0	71.2	mg	
Substance	2	Titanium	Supplier	7440-32-6	2.0	1.0	1.424	mg	
Substance	2	Copper	Supplier	7440-50-8	98.0	1.0	69.776	mg	
Material	1	Case				1.0	280.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	84.0	mg	
Substance	2	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na2S)	Supplier	26125-40-6	70.0	1.0	196.0	mg	
Material	1	COVER				1.0	37.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	11.1	mg	
Substance	2	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na2S)	Supplier	26125-40-6	70.0	1.0	25.9	mg	
Material	1	F plate_Au plating				1.0	1.4	mg	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	1.4	mg	
Material	1	M plate_Ni plating				1.0	0.4	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.4	mg	
Material	1	Knod (Actuator)				1.0	16.0	mg	
Substance	2	1,4-Benzenedicarbonylic acid, polymer with 1,2-ethanediol and 4-hydroxybenzoic acid	Supplier	25822-54-2	70.0	1.0	11.2	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	4.8	mg	
Material	1	F plate_Ni plating				1.0	1.4	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	1.4	mg	
Material	1	F plate				1.0	288.2	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.25	1.0	0.7205	mg	
Substance	2	Tin	Supplier	7440-31-5	8.0	1.0	23.056	mg	
Substance	2	Copper	Supplier	7440-50-8	91.3071428571429	1.0	263.14719	mg	
Substance	2	Iron	Supplier	7439-89-6	0.0857142857142857	1.0	0.24703	mg	

Substance	2	Zinc	Supplier	7440-66-6	0.1785714285 71429	1.0	0.51464	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.1785714285 71429	1.0	0.51464	mg	
Material	1	M plate_Au plating				1.0	0.4	mg	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	0.4	mg	