



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-04-14	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1734099-0	Amount	8385.854726	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	788319-4				100.0	30.764688	mg	
Material	2	Nickel Plate				100.0	0.6727	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	100.0	0.0013454	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	100.0	6.727E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	100.0	0.67068	mg	
Material	2	Palladium-Nickel Plate				100.0	0.015048	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	100.0	0.0120384	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	100.0	0.0030096	mg	
Material	2	Gold Plate				100.0	0.02394	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	100.0	0.0237006	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	100.0	2.394E-4	mg	
Material	2	Phos Bronze				100.0	29.3	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	100.0	0.0293	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	100.0	0.00293	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	100.0	0.0586	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	100.0	0.004395	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	100.0	26.37982	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	100.0	0.10255	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	100.0	0.00586	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	100.0	2.93E-4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	100.0	0.00293	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	100.0	0.0293	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	100.0	2.637	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	100.0	0.0293	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	100.0	1.465E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	100.0	0.00293	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	100.0	0.01465	mg	
Material	2	Tin Plate				100.0	0.753	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	100.0	7.5225E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	100.0	0.75225	mg	
Sub-Item	1	787981-6				1.0	1113.46351	mg	

Material	2	LIQUID CRYSTAL PLOYMER				1.0	1113.46351	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	33.40391	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	746.02055	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	334.03905	mg	
Sub-Item	1	796040-3				2.0	95.221708	mg	
Material	2	Brass				2.0	93.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	9.3E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	26.06093	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.0465	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0093	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.0465	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.093	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	9.3E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	66.495	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0093	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	4.65E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.186	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0465	mg	
Material	2	Nickel Plate				2.0	0.642	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.001284	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.42E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.64007	mg	
Material	2	Tin Plate				2.0	1.579708	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	2.0	0.00631883	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	1.57181	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00157971	mg	
Sub-Item	1	787681-7				1.0	4005.479	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	4005.479	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	120.16437	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	2683.67093	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1201.6437	mg	