



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	485203835	Response Date	2013-09-05	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1734375-1	Amount	11500.0	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Ni plating				1.0	0.3	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.8	1.0	0.2994	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	6.0E-4	mg	
Material	1	Housing				1.0	6384.0	mg	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	12.0	1.0	766.08	mg	
Substance	2	Graphite	Supplier	7782-42-5	13.0	1.0	829.92	mg	
Substance	2	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	40.0	1.0	2553.6	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	9.0	1.0	574.56	mg	
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	5.0	1.0	319.2	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	14.0	1.0	893.76	mg	
Substance	2	Carbon black	Supplier	1333-86-4	7.0	1.0	446.88	mg	
Material	1	Latch				1.0	92.0	mg	
Substance	2	Copper	Supplier	7440-50-8	71.5	1.0	65.78	mg	
Substance	2	Zinc	Supplier	7440-66-6	28.4	1.0	26.128	mg	
Substance	2	Iron	Supplier	7439-89-6	0.05	1.0	0.046	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.046	mg	
Material	1	Sn plating				1.0	0.3	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.3	mg	
Material	1	Side plate				1.0	902.0	mg	
Substance	2	Graphite	Supplier	7782-42-5	13.0	1.0	117.26	mg	
Substance	2	Carbon black	Supplier	1333-86-4	7.0	1.0	63.14	mg	
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	5.0	1.0	45.1	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	9.0	1.0	81.18	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	14.0	1.0	126.28	mg	
Substance	2	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	40.0	1.0	360.8	mg	

Substance	2	Talc (Mg ₃ H ₂ (SiO ₃) ₄)	Supplier	14807-96-6	12.0	1.0	108.24	mg	
Material	1	Contact				1.0	4120.8	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.2	1.0	8.2416	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	4.1208	mg	
Substance	2	Tin	Supplier	7440-31-5	9.0	1.0	370.872	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.3	1.0	12.3624	mg	
Substance	2	Copper	Supplier	7440-50-8	90.35	1.0	3723.1428	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.0604	mg	
Material	1	Gold Plating				1.0	0.3	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.15	1.0	4.5E-4	mg	
Substance	2	Gold	Supplier	7440-57-5	99.85	1.0	0.29955	mg	
Material	1	Pd-Ni plating				1.0	0.3	mg	
Substance	2	Nickel	Nickel	7440-02-0	20.0	1.0	0.06	mg	
Substance	2	Palladium	Supplier	7440-05-3	80.0	1.0	0.24	mg	