



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Sang Ho Lee	Contact Title	MGR SALES		
Company Unique ID	485203835	Response Date	2013-10-15	Contact Email	sangho@te.com				
Contact Phone Number	(82)2-3415-4533								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1565357-1	Amount	733.4	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1565358-1				1.0	733.4	mg	
Material	2	Nickel Plate				1.0	6.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0060	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	5.982	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.012	mg	
Material	2	Phos Bronze				1.0	456.2	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	431.94613	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.09124	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.04562	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	20.529	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.06843	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.4562	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.04562	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.004562	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	1.3686	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.4562	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.4562	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.04562	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.2281	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.4562	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.002281	mg	
Material	2	Tin Plate				1.0	0.4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	3.996E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.3996	mg	
Material	2	POLYAMIDE (NYLON) 4,6				1.0	269.0	mg	
Substance	3	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	34.0	1.0	91.46	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	12.0	1.0	32.28	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	80.7	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.0	1.0	8.07	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	21.0	1.0	56.49	mg	
Material	2	Gold Plate				1.0	1.8	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	1.7946	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.0054	mg	