



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	M. Global Product Compliance		
Company Unique ID	485203835	Response Date	2013-12-10	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	4-1825136-4	Amount	3875.0	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s) - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	PIANO-WIRE				1.0	30.0	mg	
Substance	2	Copper	Supplier	7440-50-8	0.01	1.0	0.0030	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.18	1.0	0.054	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.5	1.0	0.15	mg	
Substance	2	Carbon black	Supplier	1333-86-4	0.81	1.0	0.243	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.0060	1.0	0.0018	mg	
Substance	2	Tin	Supplier	7440-31-5	0.012	1.0	0.0036	mg	
Substance	2	Iron	Supplier	7439-89-6	98.482	1.0	29.5446	mg	
Material	1	DAP D72 / 6120F				1.0	350.0	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	30.0	1.0	105.0	mg	
Substance	2	1,2-Benzenedicarboxylic acid, 1,2-di-2-propen-1-yl ester, homopolymer	Supplier	25053-15-0	35.0	1.0	122.5	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	122.5	mg	
Material	1	Epoxy (MIXED RED)				1.0	50.0	mg	
Substance	2	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	2.0	1.0	1.0	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	98.0	1.0	49.0	mg	
Material	1	STEEL-BAR				1.0	150.0	mg	
Substance	2	Carbon black	Supplier	1333-86-4	0.0070	1.0	0.0105	mg	
Substance	2	Iron	Supplier	7439-89-6	99.036	1.0	148.554	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.51	1.0	0.765	mg	
Substance	2	Tin	Supplier	7440-31-5	0.07	1.0	0.105	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.0010	1.0	0.0015	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.104	1.0	0.156	mg	
Substance	2	Copper	Supplier	7440-50-8	0.0020	1.0	0.0030	mg	

Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.27	1.0	0.405	mg	6(a) Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight
Material	1	Gold-Plating				1.0	35.0	mg	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	35.0	mg	
Material	1	Copper-alloy				1.0	825.0	mg	
Substance	2	Iron	Supplier	7439-89-6	2.13	1.0	17.5725	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.07	1.0	0.5775	mg	
Substance	2	Copper	Supplier	7440-50-8	97.77	1.0	806.6025	mg	
Substance	2	Tin	Supplier	7440-31-5	0.03	1.0	0.2475	mg	
Material	1	PMC				1.0	50.0	mg	
Substance	2	2-Propenoic acid, 2-methyl-, polymer with 2-(chloromethyl)oxirane, formaldehyde, 2,5-furandione and phenol	Supplier	68492-67-1	0.05	1.0	0.025	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	99.95	1.0	49.975	mg	
Material	1	Stainless-Steel				1.0	735.0	mg	
Substance	2	Carbon black	Supplier	1333-86-4	0.045	1.0	0.33075	mg	
Substance	2	Chromium	Supplier	7440-47-3	18.16	1.0	133.476	mg	
Substance	2	Manganese	Supplier	7439-96-5	1.23	1.0	9.0405	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.026	1.0	0.1911	mg	
Substance	2	Iron	Supplier	7439-89-6	72.238	1.0	530.9493	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.0010	1.0	0.00735	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.3	1.0	2.205	mg	
Substance	2	Nickel	Nickel	7440-02-0	8.0	1.0	58.8	mg	
Material	1	BRASS-ROD				1.0	1650.0	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	3.19	1.0	52.635	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	2	Iron	Supplier	7439-89-6	0.03	1.0	0.495	mg	
Substance	2	Zinc	Supplier	7440-66-6	38.03	1.0	627.495	mg	
Substance	2	Copper	Supplier	7440-50-8	58.05	1.0	957.825	mg	
Substance	2	Tin	Supplier	7440-31-5	0.7	1.0	11.55	mg	