



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Kim, Seong Kyung	Contact Title	Account Manager		
Company Unique ID	TE Connectivity	Response Date	2014-10-10	Contact Email	sophie.kim@te.com				
Contact Phone Number	82-2-3415-4614								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	3-1462037-0	Amount	1231.339	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	5-1462115-7				1.0	441.177	mg	
Material	2	1001647-9				1.0	147.08	mg	
Substance	3	Copper	Supplier	7440-50-8	97.63	1.0	143.5942	mg	
Substance	3	2-Oxepanone, polymer with 1,4-butanediol and 1,1-methylenebis[4 - isocyanatocyclohexane]	Supplier	53504-41-9	2.37	1.0	3.4858	mg	
Material	2	Copper Alloy				1.0	12.327	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.012327	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.2	1.0	0.024654	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.5	1.0	0.061635	mg	
Substance	3	Copper	Supplier	7440-50-8	85.2175	1.0	10.50476	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	1.2327E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.2327E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0012327	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	1.0	0.073962	mg	
Substance	3	Tin	Supplier	7440-31-5	2.8	1.0	0.34516	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0012327	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0012327	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.5	1.0	1.29433	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	6.1635E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0061635	mg	
Material	2	Yoke				1.0	55.4	mg	
Substance	3	Iron	Supplier	7439-89-6	100.0	1.0	55.4	mg	
Material	2	LCP-GF30				1.0	112.9	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	33.87	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.4	1.0	0.4516	mg	

Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.6	1.0	78.5784	mg	
Material	2	LCP				1.0	112.87	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	45.148	mg	
Substance	3	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	60.0	1.0	67.722	mg	
Material	2	permanent magnet				1.0	0.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	16.3	1.0	0.0	mg	
Substance	3	Iron	Supplier	7439-89-6	54.46	1.0	0.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	29.24	1.0	0.0	mg	
Material	2	Yoke Ni-Plating				1.0	0.6	mg	
Substance	3	Nickel	Nickel	7440-02-0	100.0	1.0	0.6	mg	
Sub-Item	1	5-1462112-6				1.0	635.292	mg	
Material	2	D02684 Contact				1.0	1.682	mg	
Substance	3	Titanium	Supplier	7440-32-6	0.2	1.0	0.003364	mg	
Substance	3	Gold	Supplier	7440-57-5	4.3	1.0	0.072326	mg	
Substance	3	Iron	Supplier	7439-89-6	0.3	1.0	0.005046	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	0.006728	mg	
Substance	3	Silver	Supplier	7440-22-4	18.6	1.0	0.31285	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.1	1.0	0.001682	mg	
Substance	3	Palladium	Supplier	7440-05-3	27.8	1.0	0.4676	mg	
Substance	3	Copper	Supplier	7440-50-8	33.0	1.0	0.55506	mg	
Substance	3	Nickel	Nickel	7440-02-0	15.3	1.0	0.25735	mg	
Material	2	Nickel Plate				1.0	18.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.036	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.018	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	17.946	mg	
Material	2	Palladium plate				1.0	10.0	mg	
Substance	3	Palladium	Supplier	7440-05-3	100.0	1.0	10.0	mg	
Material	2	LCP-GF30				1.0	40.19	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	12.057	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.4	1.0	0.16076	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.6	1.0	27.97224	mg	
Material	2	Copper Alloy				1.0	552.4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.2762	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	1.0	5.524	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	1.0	6.6288	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.5524	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7635	1.0	512.42557	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	0.33144	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.005524	mg	

Substance	3	Magnesium	Supplier	7439-95-4	0.3	1.0	1.6572	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	1.0	0.5524	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	1.0	1.1048	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.05524	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.05524	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	1.0	23.2008	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.02762	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.002762	mg	
Material	2	Gold Plate				1.0	13.02	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	12.98094	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.03906	mg	
Sub-Item	1	1-1462112-0				1.0	129.87	mg	
Material	2	LCP				1.0	129.87	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	51.948	mg	
Substance	3	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	60.0	1.0	77.922	mg	
Sub-Item	1	5-1462110-0				1.0	25.0	mg	
Material	2	resin				1.0	25.0	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2,2-[[1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis[oxirane]	Supplier	25036-25-3	100.0	1.0	25.0	mg	