





© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: PQFP, 144 LEAD 28 X 28 X 3.7 PKG, 0.65 PITCH	DOCUMENT NO: 98ASB42783B REV: D	
	STANDARD: NON-JEDEC	
	11 SEP 2014	

NOTES:

1. DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M–1994.
3. DATUMS A–B AND D TO BE DETERMINED AT DATUM PLANE H.

△4. THIS DIMENSION DOES NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS 0.25MM PER SIDE. THIS DIMENSION IS MAXIMUM PLASTIC BODY SIZE DIMENSION INCLUDING MOLD MISMATCH.

△5. DIMENSIONS TO BE DETERMINED AT SEATING PLANE, DATUM C.

△6. DIMENSIONS TO BE DETERMINED AT DATUM PLANE H.

© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: PQFP, 144 LEAD 28 X 28 X 3.7 PKG, 0.65 PITCH	DOCUMENT NO: 98ASB42783B REV: D	
	STANDARD: NON-JEDEC	
	12 SEP 2014	