



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-05-28	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-5353512-0	Amount	70.5	Version	-	Identity			
Manufacturer Item Name	ON TAPING (EMBOSS) 0.5MM FS CO	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	REF. ASSY 1.5MM VERSION 0.5 FS CONN. WIT				1.0	70.5	mg	
Material	2	Phos Bronze				1.0	9.328	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	8.83208	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0018656	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	9.328E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	0.41976	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.0013992	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.009328	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	9.328E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	9.328E-5	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.027984	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.009328	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.009328	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	9.328E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.004664	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.009328	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.664E-5	mg	
Material	2	Nickel Plate				1.0	0.9995	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001999	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	9.995E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.9965	mg	
Material	2	PPA-GF30				1.0	41.0	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	21.0	1.0	8.61	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0020	1.0	8.2E-4	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.7	1.0	0.287	mg	
Substance	3	Magnesium oxide (MgO)	Supplier	1309-48-4	6.0	1.0	2.46	mg	

Substance	3	Antimonate (SbO3 ¹⁻), sodium (1:1)	Supplier	15432-85-6	2.0	1.0	0.82	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	23.9991	1.0	9.83963	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	44.2959	1.0	18.16132	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	0.82	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0020	1.0	8.2E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0010	1.0	4.1E-4	mg	
Material	2	Tin Plate				1.0	0.55	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	5.4945E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.54945	mg	
Material	2	Phos Bronze				1.0	18.5025	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0185025	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00185025	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.037005	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.00277538	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	1.0	16.65845	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0037005	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.06475875	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.8503E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.0185025	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.00185025	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	1.66523	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.0185025	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.25125E-5	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00185025	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.00925125	mg	
Material	2	Gold Plate				1.0	0.12	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	1.0	0.1188	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	0.0012	mg	