






TOP VIEW



BOTTOM VIEW



SIDE VIEW

|                                                                 |                           |                            |             |
|-----------------------------------------------------------------|---------------------------|----------------------------|-------------|
| © FREESCALE SEMICONDUCTOR, INC.<br>ALL RIGHTS RESERVED.         | <b>MECHANICAL OUTLINE</b> | PRINT VERSION NOT TO SCALE |             |
| TITLE:<br>LGA 16 I/O,<br>3 X 3 X 0.5 PITCH,<br>SENSOR, 1 MM PKG | DOCUMENT NO: 98ASA00287D  |                            | REV: 0      |
|                                                                 | CASE NUMBER: 2094-01      |                            | 21 OCT 2010 |
|                                                                 | STANDARD: NON-JEDEC       |                            |             |

NOTES:

1. ALL DIMENSIONS IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
3. DIMENSIONS ARE SYMETRIC ABOUT THE CENTERLINES UNLESS DIMENSIONED OTHERWISE.

|                                                              |  |                           |                          |                            |             |
|--------------------------------------------------------------|--|---------------------------|--------------------------|----------------------------|-------------|
| © FREESCALE SEMICONDUCTOR, INC.<br>ALL RIGHTS RESERVED.      |  | <b>MECHANICAL OUTLINE</b> |                          | PRINT VERSION NOT TO SCALE |             |
| TITLE: LGA 16 I/O,<br>3 X 3 X 0.5 PITCH,<br>SENSOR, 1 MM PKG |  |                           | DOCUMENT NO: 98ASA00287D |                            | REV: 0      |
|                                                              |  |                           | CASE NUMBER: 2094-01     |                            | 21 OCT 2010 |
|                                                              |  |                           | STANDARD: NON-JEDEC      |                            |             |