




| DIM | MILLIMETERS<br>MIN | MILLIMETERS<br>MAX | DIM | MILLIMETERS<br>MIN | MILLIMETERS<br>MAX | NOTES:<br><br>1. DIMENSIONS ARE IN MILLIMETERS.<br>2. DIMENSIONS AND TOLERANCES PER<br>ASME Y14.5M-1994.<br>3. STYLE 1:<br><br>PIN 1: GROUND<br>2: + OUTPUT<br>3: + SUPPLY<br>4: - OUTPUT |
|-----|--------------------|--------------------|-----|--------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| A   | 29.08              | 29.85              | N   | 10.67              | 11.18              |                                                                                                                                                                                           |
| B   | 17.40              | 18.16              | P   | Ø3.89              | Ø4.04              |                                                                                                                                                                                           |
| C   | 10.29              | 11.05              | Q   | Ø3.89              | Ø4.04              |                                                                                                                                                                                           |
| D   | 0.41               | 0.51               | R   | 1.60               | 2.11               |                                                                                                                                                                                           |
| F   | 1.22               | 1.63               | S   | 5.59               | 6.10               |                                                                                                                                                                                           |
| G   | 2.54 BSC           |                    | U   | 23.11 BSC          |                    |                                                                                                                                                                                           |
| H   | Ø4.62              | Ø4.93              | V   | 6.30               | 7.06               |                                                                                                                                                                                           |
| J   | 0.36               | 0.41               | W   | 7.89               | 8.38               |                                                                                                                                                                                           |
| K   | 17.65              | 18.42              |     |                    |                    |                                                                                                                                                                                           |
| L   | 7.37               | 7.62               |     |                    |                    |                                                                                                                                                                                           |

TITLE:  
SENSOR, 4 LEAD UNIBODY

CASE NUMBER: 344C-01

STANDARD: NON-JEDEC

PACKAGE CODE:IN AGILE SHEET: 1 OF 2