


DOCUMENT NO: 98ASB42797B

PAGE: 867C

DO NOT SCALE THIS DRAWING

REV: G



DIM	MILLIMETERS MIN MAX		DIM	MILLIMETERS MIN MAX		NOTES: 1. DIMENSIONS ARE IN MILLIMETERS. 2. DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994. 3. 867C-01 THRU -04 OBSOLATE, NEW STANDARD 867C-05. 3. STYLE 1: PIN 1: V OUT 5: V2 2: GROUND 6: V EX 3: VCC 4: V1
A	29.08	29.85	P	ø3.89	ø4.04	
B	17.40	18.16	Q	ø3.89	ø4.04	
C	10.29	11.05	R	1.60	2.11	
D	0.68	0.84	S	5.59	6.10	
F	1.22	1.63	U	23.11	BSC	
G	2.54	BSC	V	4.62	4.93	
J	0.36	0.41	W	7.87	8.38	
K	17.65	18.42	X	6.30	7.06	
L	7.37	7.62				
N	10.67	11.18				

TITLE:

SENSOR, 4 LEAD UNIBODY

CASE NUMBER: 867C-05

STANDARD: NON-JEDEC

PACKAGE CODE:IN AGILE

SHEET: 1 OF 2