

PART INFORMATION		
Mfg Item Number		MK20FX512VMD12
Mfg Item Name		MAPBGA 144 13*13*1.7 P1
SUPPLIER		
Company Name		Freescale Semiconductor Inc
Company Unique ID		14-141-7928
Response Date		2015-06-18
Response Document ID		007BK00169D010A1.8
Contact Name		Freescale Semiconductor Inc
Contact Title		Product Technical Support
Contact Phone		1-800-521-6274
Contact Email		support@freescale.com
Authorized Representative		Daniel Binyon
Representative Title		EPP Customer Response
Representative Phone		512-895-3406
Representative Email		eppanlst@freescale.com
URL for Additional Information		www.freescale.com
DECLARATION		
EU RoHS		Yes
Pb Free		Yes
HalogenFree		Yes
Plating Indicator		e1
EU RoHS Exemption(s)		
MANUFACTURING		
Mfg Item Number		MK20FX512VMD12
Mfg Item Name		MAPBGA 144 13*13*1.7 P1
Version		ALL
Weight		0.441000
UoM		g
Unit Volume		EACH
J-STD-020 MSL Rating		3
Peak Processing Temperature		260 C
Max Time at Peak Temperature		40 seconds
Number of Processing Cycles		3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Solder Balls - Lead Free	0.0734						g					
Solder Balls - Lead Free		Metals	Aluminum, metal	7429-90-5		0.00000228	g	31	0.0031		5	0.0005
Solder Balls - Lead Free		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.00000918	g	125	0.0125		20	0.002
Solder Balls - Lead Free		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000543	g	74	0.0074		12	0.0012
Solder Balls - Lead Free		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00001373	g	187	0.0187		31	0.0031
Solder Balls - Lead Free		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000088	g	12	0.0012		1	0.0001
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8		0.00036656	g	4994	0.4994		831	0.0831
Solder Balls - Lead Free		Metals	Gold, metal	7440-57-5		0.00000455	g	62	0.0062		10	0.001
Solder Balls - Lead Free		Metals	Indium, metal	7440-74-6		0.00000455	g	62	0.0062		10	0.001
Solder Balls - Lead Free		Solvents, additives, and other materials	Sulfur	7704-34-9		0.00000044	g	6	0.0006		0	0
Solder Balls - Lead Free		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00000455	g	62	0.0062		10	0.001
Solder Balls - Lead Free		Metals	Iron, metal	7439-89-6		0.00000918	g	125	0.0125		20	0.002
Solder Balls - Lead Free		Lead/Lead Compounds	Lead	7439-92-1		0.00002753	g	375	0.0375		62	0.0062
Solder Balls - Lead Free		Nickel (external applications only)	Nickel	7440-02-0		0.00000228	g	31	0.0031		5	0.0005
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4		0.00283255	g	39953	3.9953		6649	0.6649
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5		0.07001492	g	953882	95.3882		158763	15.8763
Solder Balls - Lead Free		Metals	Zinc, metal	7440-66-6		0.00000139	g	19	0.0019		3	0.0003
Non-Conductive Epoxy/Adhesive	0.0015						g					
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.0001125	g	75000	7.5		255	0.0255
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5		0.0003	g	200000	20		680	0.068
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-		0.0001125	g	75000	7.5		255	0.0255
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-		0.0003	g	200000	20		680	0.068
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	80676-86-0		0.000675	g	450000	45		1530	0.153
Bonding Wire, Copper	0.0037						g					
Bonding Wire, Copper		Metals	Copper, metal	7440-50-8		0.003589	g	970000	97		8138	0.8138
Bonding Wire, Copper		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.000111	g	30000	3		251	0.0251
Die Encapsulant, Halogen-free	0.2362						g					
Die Encapsulant, Halogen-free		Metals	Other aluminum compounds	-		0.007086	g	30000	3		16068	1.6068
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.002362	g	10000	1		5356	0.5356
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.007086	g	30000	3		16068	1.6068
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.007086	g	30000	3		16068	1.6068
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	80676-86-0		0.20077	g	850000	85		455278	45.5278
Die Encapsulant, Halogen-free		Plastics/polymers	Other Non-halogenated Epoxy resins	-		0.01181	g	50000	5		26780	2.678
Silicon Semiconductor Die	0.0142						g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.000284	g	20000	2		643	0.0643
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.013916	g	980000	98		31555	3.1555
Organic Substrate	0.112						g					
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.00353797	g	31589	3.1589		8022	0.8022
Organic Substrate		Metals	Copper, metal	7440-50-8		0.04124984	g	368302	36.8302		93537	9.3537
Organic Substrate		Plastics/polymers	Epikote 862	28064-14-4		0.00858499	g	76741	7.6741		19489	1.9489
Organic Substrate		Plastics/polymers	Formaldehyde, polymer with 2-methylphenol, glycidyl ether	64425-89-4		0.00548128	g	48940	4.894		12429	1.2429
Organic Substrate		Metals	Gold, metal	7440-57-5		0.0002931	g	2617	0.2617		664	0.0664
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.00228994	g	20437	2.0437		5190	0.519
Organic Substrate		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.00469347	g	41906	4.1906		10642	1.0642
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.02874771	g	256676	25.6676		65187	6.5187
Organic Substrate		Glass	Silicon dioxide	7631-86-9		0.00246411	g	22001	2.2001		5587	0.5587
Organic Substrate		Solvents, additives, and other materials	Other Aromatic carbonyl compounds	-		0.00056806	g	5072	0.5072		1288	0.1288
Organic Substrate		Metals	Aluminum Hydroxide	21645-51-2		0.01408053	g	125719	12.5719		31928	3.1928

LINKS	
MCD LINK	
Freescal website	http://www.freescal.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescal_Response.pdf
China RoHS	http://www.freescal.com/chinarohs
REACH signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescal_Response.pdf
ELV signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescal_Reponse.pdf
Conflict Minerals statement	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescal_Response.pdf
FREESCALE ENVIRONMENTAL INFORMATION	
EPP website	http://www.freescal.com/epp
FAQ	http://www.freescal.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ
Technical Service Request	https://www.freescal.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.freescal.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MK20FX512VMD12_IPC1752_v11.xml

http://www.freescale.com/mcds/MK20FX512VMD12_IPC1752A.xml