

PART INFORMATION

Mfg Item Number	T1020NSN7WQB
Mfg Item Name	FCPBGA 780 23*23*1.92

SUPPLIER

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2015-06-11
Response Document ID	00FAK50008S314M1.0
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

DECLARATION

EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e1
EU RoHS Exemption(s)	

MANUFACTURING

Mfg Item Number	T1020NSN7WQB
Mfg Item Name	FCPBGA 780 23*23*1.92
Version	ALL
Weight	1.482800
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	250 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Solder Balls - Lead Free	0.1936						g				
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8		0.0006974	g	5009	0.5009	653	0.0653
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4		0.00581845	g	30054	3.0054	3923	0.3923
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5		0.18681181	g	964937	96.4937	125985	12.5985
Underfill	0.0138						g				
Underfill		Bismuth/Bismuth Compounds	Bismuth nitrate	10361-44-1		0.000069	g	5000	0.5	46	0.0046
Underfill		Bismuth/Bismuth Compounds	Bismuth trioxide	1304-76-3		0.000069	g	5000	0.5	46	0.0046
Underfill		Plastics/polymers	1,6-Bis(2,3-epoxypropoxy) naphthalene	27610-48-6		0.00207	g	150000	15	1396	0.1396
Underfill		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.00138	g	100000	10	930	0.093
Underfill		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.000069	g	5000	0.5	46	0.0046
Underfill		Plastics/polymers	4,4'-Isopropylidenediphenol-1-chloro-2,3-epoxypropane concentrate	25068-38-6		0.000414	g	30000	3	279	0.0279
Underfill		Glass	Silica, vitreous	60676-86-0		0.00298	g	600000	60	5594	0.5594
Underfill		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.000069	g	5000	0.5	46	0.0046
Underfill		Solvents, additives, and other materials	Proprietary Material-Other aliphatic amine compounds	-		0.00138	g	100000	10	930	0.093
Organic Substrate, Halogen-free	1.1522						g				
Organic Substrate, Halogen-free		Metals	Barium sulfate	7727-43-7		0.00991827	g	7827	0.7827	6081	0.6081
Organic Substrate, Halogen-free		Metals	Copper, metal	7440-50-8		0.40546495	g	251905	25.1905	273461	27.3461
Organic Substrate, Halogen-free		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.1838819	g	159692	15.9692	124009	12.4009
Organic Substrate, Halogen-free		Metals	Talc	14807-96-6		0.00103252	g	897	0.0897	697	0.0697
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Proprietary Material-Other organic phosphorous compounds	-		0.01294295	g	10886	1.0886	8458	0.8458
Organic Substrate, Halogen-free		Plastics/polymers	4,4'-Isopropylidenediphenol-1-chloro-2,3-epoxypropane concentrate	25068-38-6		0.01411099	g	12247	1.2247	9516	0.9516
Organic Substrate, Halogen-free		Plastics/polymers	Proprietary Material-Other polymers	-		0.11522	g	100000	10	77704	7.7704
Organic Substrate, Halogen-free		Glass	Fibrous-glass-wool	65997-17-3		0.21712748	g	186446	18.6446	146430	14.643
Organic Substrate, Halogen-free		Glass	Silicon dioxide	7631-86-9		0.0068372	g	51933	5.1933	40354	4.0354
Organic Substrate, Halogen-free		Metals	Silver, metal	7440-22-4		0.00056112	g	487	0.0487	378	0.0378
Organic Substrate, Halogen-free		Metals	Tin, metal	7440-31-5		0.01805152	g	15687	1.5687	12173	1.2173
Organic Substrate, Halogen-free		Metals	Aluminum Hydroxide	21645-51-2		0.11529259	g	100063	10.0063	77753	7.7753
Organic Substrate, Halogen-free		Metals	Copper phthalocyanine	147-14-8		0.00005781	g	50	0.005	38	0.0038
Pb-free Bumped Semiconductor D	0.1232						g				
Pb-free Bumped Semiconductor D		Nickel (external applications only)	Nickel	7440-02-0		0.000816	g	5000	0.5	415	0.0415
Pb-free Bumped Semiconductor D		Metals	Silver, metal	7440-22-4		0.00038808	g	3150	0.315	261	0.0261
Pb-free Bumped Semiconductor D		Metals	Tin, metal	7440-31-5		0.01089992	g	86950	8.695	7216	0.7216
Pb-free Bumped Semiconductor D		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.0010288	g	9000	0.9	747	0.0747
Pb-free Bumped Semiconductor D		Glass	Silicon, doped	-		0.1103872	g	896000	89.6	74445	7.4445

LINKS

MCD LINK

Freescale website <http://www.freescale.com>

GENERAL ENVIRONMENTAL COMPLIANCE LINKS

RoHS signed letter http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescale_Response.pdf

China RoHS <http://www.freescale.com/chinarohs>

REACH signed letter http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescale_Response.pdf

ELV signed letter http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescale_Reponse.pdf

Conflict Minerals statement http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescale_Response.pdf

FREESCALE ENVIRONMENTAL INFORMATION

EPP website <http://www.freescale.com/epp>

FAQ http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ

Technical Service Request https://www.freescale.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod

LINKS TO BLANK IPC1752 FORMS

Blank IPC1752 v1.1 Form http://www.freescale.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/T1020NSN7WQB_IPC1752_v11.xml

http://www.freescale.com/mcds/T1020NSN7WQB_IPC1752A.xml