

PART INFORMATION	
Mfg Item Number	T1022NXE7MQB
Mfg Item Name	FCPBGA 780 23*23*1.92
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2015-06-10
Response Document ID	00FAK50008S314A1.2
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e1
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	T1022NXE7MQB
Mfg Item Name	FCPBGA 780 23*23*1.92
Version	ALL
Weight	1.482800
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	250 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Solder Balls - Lead Free	0.1936						g					
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8		0.00096974	g	5009	0.5009		653	0.0053
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4		0.00581845	g	30054	3.0054		3923	0.3923
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5		0.18681181	g	964937	96.4937		125985	12.5985
Underfill	0.0138						g					
Underfill		Bismuth/Bismuth Compounds	Bismuth nitrate	10361-44-1		0.000069	g	5000	0.5		46	0.0046
Underfill		Bismuth/Bismuth Compounds	Bismuth trioxide	1304-76-3		0.000069	g	5000	0.5		46	0.0046
Underfill		Plastics/polymers	1,6-Bis(2,3-epoxypropoxy) naphthalene	27610-48-6		0.00207	g	150000	15		1396	0.1396
Underfill		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.00138	g	100000	10		930	0.093
Underfill		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.000069	g	5000	0.5		46	0.0046
Underfill		Plastics/polymers	4,4'-Isopropylidenediphenol-1-chloro-2,3-epoxypropane concentrate	25068-38-6		0.000414	g	30000	3		279	0.0279
Underfill		Glass	Silica, vitreous	60676-86-0		0.00828	g	600000	60		5584	0.5584
Underfill		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.000069	g	5000	0.5		46	0.0046
Underfill		Solvents, additives, and other materials	Proprietary Material-Other aliphatic amine compounds	-		0.00138	g	100000	10		930	0.093
Organic Substrate, Halogen-free	1.1522						g					
Organic Substrate, Halogen-free		Metals	Barium sulfate	7727-43-7		0.00901827	g	7827	0.7827		6081	0.6081
Organic Substrate, Halogen-free		Metals	Copper, metal	7440-50-8		0.40546495	g	351905	35.1905		273461	27.3461
Organic Substrate, Halogen-free		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.1838619	g	159592	15.9592		124009	12.4009
Organic Substrate, Halogen-free		Metals	Talc	14807-96-6		0.00103252	g	897	0.0897		697	0.0697
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Proprietary Material-Other organic phosphorous compounds	-		0.01254295	g	10886	1.0886		8459	0.8458
Organic Substrate, Halogen-free		Plastics/polymers	4,4'-Isopropylidenediphenol-1-chloro-2,3-epoxypropane concentrate	25068-38-6		0.01411099	g	12247	1.2247		9516	0.9516
Organic Substrate, Halogen-free		Plastics/polymers	Proprietary Material-Other polymers	-		0.11522	g	100000	10		77704	7.7704
Organic Substrate, Halogen-free		Glass	Fibrous-glass-wool	65997-17-3		0.21712748	g	186446	18.6446		146430	14.643
Organic Substrate, Halogen-free		Glass	Silicon dioxide	7631-86-9		0.0986372	g	51933	5.1933		40354	4.0354
Organic Substrate, Halogen-free		Metals	Silver, metal	7440-22-4		0.00056112	g	487	0.0487		378	0.0378
Organic Substrate, Halogen-free		Metals	Tin, metal	7440-31-5		0.01805152	g	15667	1.5667		12173	1.2173
Organic Substrate, Halogen-free		Metals	Aluminum Hydroxide	21645-51-2		0.11529259	g	100063	10.0063		77753	7.7753
Organic Substrate, Halogen-free		Metals	Copper phthalocyanine	147-14-8		0.00005781	g	50	0.005		38	0.0038
Pb-free Bumped Semiconductor D	0.1232						g					
Pb-free Bumped Semiconductor D		Nickel (external applications only)	Nickel	7440-02-0		0.000816	g	5000	0.5		415	0.0415
Pb-free Bumped Semiconductor D		Metals	Silver, metal	7440-22-4		0.00038808	g	3150	0.315		261	0.0261
Pb-free Bumped Semiconductor D		Metals	Tin, metal	7440-31-5		0.01069992	g	86950	8.6895		7216	0.7216
Pb-free Bumped Semiconductor D		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0011088	g	9000	0.9		747	0.0747
Pb-free Bumped Semiconductor D		Glass	Silicon, doped	-		0.1103872	g	896000	89.6		74445	7.4445

LINKS	
MCD LINK	
Freescal website	http://www.freescal.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescal_Response.pdf
China RoHS	http://www.freescal.com/chinarohs
REACH signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescal_Response.pdf
ELV signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescal_Reponse.pdf
Conflict Minerals statement	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescal_Response.pdf
FREESCALE ENVIRONMENTAL INFORMATION	
EPP website	http://www.freescal.com/epp
FAQ	http://www.freescal.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ
Technical Service Request	https://www.freescal.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.freescal.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/T1022NXE7MQB_IPC1752_v11.xml

http://www.freescale.com/mcds/T1022NXE7MQB_IPC1752A.xml