



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com																													
Contact Phone Number		1-717-592-4423																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-104068-1	Amount	1493.087666	Version	-	Identity																												
Manufacturer Item Name	24 SYSTEM 50 HDR DRST SHRD	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions																																	
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	24 SYSTEM 50 HDR HSG DR LATCH				1.0	970.41533	mg																										
Material	2	LIQUID CRYSTAL PLOYMER				1.0	970.41533	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	29.11246	mg																										
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	650.17827	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	291.1246	mg																										
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX				24.0	21.778014	mg																										
Material	2	Nickel Plate				24.0	0.21	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	24.0	4.2E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	24.0	2.1E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	24.0	0.20937	mg																										
Material	2	Gold Plate				24.0	0.17	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	24.0	0.16949	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	24.0	5.1E-4	mg																										
Material	2	Brass				24.0	20.738014	mg																										
Substance	3	Tin	Supplier	7440-31-5	0.1	24.0	0.02073801	mg																										
Substance	3	Copper	Supplier	7440-50-8	64.0	24.0	13.27233	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	24.0	0.01036901	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	24.0	2.0738E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	24.0	0.0020738	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	24.0	0.02073801	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.1	24.0	0.02073801	mg																										
Substance	3	Zinc	Supplier	7440-66-6	35.2085	24.0	7.30154	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	24.0	0.0020738	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	24.0	0.0020738	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.05	24.0	0.01036901	mg																										

Substance	3	Nickel	Nickel	7440-02-0	0.3	24.0	0.06221404	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	24.0	0.0020738	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	24.0	1.0369E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	24.0	0.01036901	mg	
Material	2	Gold Plate				24.0	0.17	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	24.0	5.1E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	24.0	0.16949	mg	
Material	2	Tin-Lead Plate				24.0	0.49	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	24.0	0.45227	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	24.0	0.00343	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	24.0	0.0343	mg	