



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	TE Connectivity	Response Date	2015-07-29	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	323676	Amount	972.311431	Version	-	Identity																												
Manufacturer Item Name	TERMINAL,PID G R 16-14 4	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	SLEEVE ASSEMBLY 16-14				1.0	407.096	mg																										
Material	2	Copper				1.0	293.155	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.14658	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00293155	mg																										
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	292.26821	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00293155	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0293155	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0293155	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.058631	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.29316	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.29316	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00146577	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0293155	mg																										
Material	2	Tin Plate				1.0	7.429	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	7.39185	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.029716	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.007429	mg																										
Material	2	COLORANT				1.0	2.13024	mg																										
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.32	1.0	0.00681677	mg																										
Substance	3	3H-Naphtho[1,2,3-de]quinoline-2,7-dione, 3-methyl-6-[(4-methylphenyl)amino]-	Supplier	81-39-0	0.1	1.0	0.00213024	mg																										
Substance	3	Octadecanamide, N,N-1,2-ethanediyldis-	Supplier	110-30-5	0.0090	1.0	1.9172E-4	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	98.98	1.0	2.10851	mg																										
Substance	3	Carbon black	Supplier	1333-86-4	0.0010	1.0	2.13024E-5	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.17	1.0	0.00362141	mg	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.42	1.0	0.00894701	mg	
Material	2	PA66				1.0	104.38176	mg	
Substance	3	Phosphoric acid	Supplier	7664-38-2	0.075	1.0	0.07828632	mg	
Substance	3	Acetic acid	Supplier	64-19-7	0.015	1.0	0.01565726	mg	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	89.39	1.0	93.30686	mg	
Substance	3	Acetic acid, copper(2) salt (2:1)	Supplier	142-71-2	0.02	1.0	0.02087635	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	10.43818	mg	
Substance	3	Potassium bromide	Supplier	7758-02-3	0.5	1.0	0.52191	mg	
Sub-Item	1	TERMINAL,BU DG R 16-14 4				1.0	565.215431	mg	
Material	2	Copper				1.0	559.276	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.27964	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00559276	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	557.58419	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00559276	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0559276	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0559276	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.11186	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.55928	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.55928	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00279638	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0559276	mg	
Material	2	Tin Plate				1.0	5.939431	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	5.90973	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.02375772	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00593943	mg	