



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com				
Contact Phone Number	1-717-592-4423								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-147377-1	Amount	903.6743024	Version	-	Identity			
Manufacturer Item Name	10 SYS50 SMT HDR DR SHD SN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	10 SYS 50 SMT SHRD DR HDR HSG				1.0	580.0	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	580.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	17.4	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	388.6	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	174.0	mg	
Sub-Item	1	SYS 50 HEADER VACUUM COVER				1.0	88.532	mg	
Material	2	Aluminum Alloy				1.0	88.532	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	1.0	0.088532	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.05	1.0	0.044266	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.35	1.0	0.30986	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.05	1.0	0.044266	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	1.0	0.35413	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.25	1.0	0.22133	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.05	1.0	0.044266	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.05	1.0	0.044266	mg	
Substance	3	Aluminum	Supplier	7429-90-5	95.5945	1.0	84.63172	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	0.088532	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.1	1.0	0.088532	mg	
Substance	3	Magnesium	Supplier	7439-95-4	2.8	1.0	2.4789	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.044266	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.4266E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.044266	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0044266	mg	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				10.0	23.51423024	mg	
Material	2	Tin Plate				10.0	0.0746	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.07452547	mg	
Material	2	Nickel Plate				10.0	0.137	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	2.74E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	1.37E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.13659	mg	
Material	2	Brass				10.0	23.24	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	10.0	0.02324	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	10.0	14.8736	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	10.0	0.01162	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	2.324E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	10.0	0.002324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.02324	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	10.0	0.02324	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	10.0	8.18246	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.002324	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.002324	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	10.0	0.01162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	10.0	0.06972	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.002324	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	1.162E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.01162	mg	
Material	2	Gold Plate				10.0	0.0602	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.0600194	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	1.806E-4	mg	
Material	2	Gold Plate				10.0	0.00243024	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.00242295	mg	