



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-08-20	Contact Email	jp.kuntz@te.com																													
Contact Phone Number		717-986-5932																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-1437581-4	Amount	1571.652484	Version	-	Identity																												
Manufacturer Item Name	ASE42=4PDT AUTO-SLIDE	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions																																	
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	11541-02=SLIDER 2 POS AUTOSLID				4.0	41.14	mg																										
Material	2	Nickel Plate				4.0	0.34	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	6.8E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	3.4E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.33898	mg																										
Material	2	Beryllium Copper				4.0	39.8	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	2.0	4.0	0.796	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	4.0	0.00398	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.00796	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.2	4.0	0.0796	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.2	4.0	0.0796	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.4	4.0	0.1592	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.00398	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.2	4.0	0.0796	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	4.0	3.98E-4	mg																										
Substance	3	Copper	Supplier	7440-50-8	96.649	4.0	38.4663	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	0.0398	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	4.0	0.0796	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	0.00199	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	1.99E-4	mg																										
Material	2	Silver Plate				4.0	1.0	mg																										
Substance	3	Silver	Supplier	7440-22-4	98.0	4.0	0.98	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	4.0	0.02	mg																										
Sub-Item	1	ACTUATOR, 4PDT TOP TALL				1.0	218.2	mg																										
Material	2	PA36-GF30				1.0	218.2	mg																										
Substance	3	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	43.886	1.0	95.75925	mg																										

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.5	1.0	42.549	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	65.46	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.5	1.0	12.001	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	2.4002	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0060	1.0	0.013092	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0080	1.0	0.017456	mg	
Sub-Item	1	COVER, 4PDT TOP, OPEN				1.0	201.5	mg	
Material	2	PCT-GF30				1.0	201.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	31.0	1.0	62.465	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	6.0	1.0	12.09	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.5	1.0	7.0525	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	14.0	1.0	28.21	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.7	1.0	1.4105	mg	
Substance	3	Talc (Mg3H2(SiO3) 4)	Supplier	14807-96-6	2.0	1.0	4.03	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	42.8	1.0	86.242	mg	
Sub-Item	1	BASE, 4 POLE AG & SN/PB				1.0	987.392484	mg	
Material	2	PCT-GF30				1.0	463.3	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	31.0	1.0	143.623	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	6.0	1.0	27.798	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.5	1.0	16.2155	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	14.0	1.0	64.862	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.7	1.0	3.2431	mg	
Substance	3	Talc (Mg3H2(SiO3) 4)	Supplier	14807-96-6	2.0	1.0	9.266	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	42.8	1.0	198.2924	mg	
Material	2	Tin-Lead Plate				1.0	0.239484	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	1.0	0.22104	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	1.0	0.00167639	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	1.0	0.01676388	mg	
Material	2	Nickel Plate				1.0	0.091	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	1.82E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	9.1E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.090727	mg	
Material	2	Brass				1.0	523.7	mg	

Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.005237	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	146.75383	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.26185	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.05237	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.26185	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.5237	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	374.4455	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.005237	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.05237	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0026185	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.0474	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.026185	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.26185	mg	
Material	2	Silver Plate				1.0	0.062	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.00124	mg	
Substance	3	Silver	Supplier	7440-22-4	98.0	1.0	0.06076	mg	