



- 1 DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2 MATERIAL: HOUSING— POLYCARBONATE, CLEAR
TERMINAL— .305 [.012] THICK PHOSPHOR BRONZE PLATED WITH .127 μ m [.00005] MINIMUM THICK GOLD IN LOCALIZED PLATE AREA OVER 2.54 μ m [.000100] MINIMUM THICK NICKEL UNDERPLATE.

SHIELD, OPTIONAL— COPPER ALLOY WITH 1.27 μ m [.000050] MINIMUM SEMI-BRIGHT (SATIN) NICKEL.
3. PLUG WILL ACCEPT 24–26 AWG STRANDED CONDUCTOR WITH A SINGLE INSULATION OF 0.89–0.99 [.035–.039] OR 23–24 AWG SOLID CONDUCTOR WITH A SINGLE INSULATION OF 0.89–0.99 [.035–.039].
4. PLUG WILL ACCEPT A CABLE WITH A PLIABLE JACKET OF $\varnothing$ 4.83 [.190] TO 5.59 [.220] OR A RIGID JACKET OF $\varnothing$ 4.83 [.190] TO 5.08 [.200].
- 5 TERMINATED DIMENSION 5.89 [.232] – 6.15 [.242].
6. UL RECOGNIZED FILE NUMBER E81956.



SHIELDED

100	6-569550-3	MP-5ES-1
500	6-569550-2	MP-5ES-5
PACKAGE	MATERIAL	CATALOG NUMBER
SHIELDED CATALOG NUMBER VERSIONS		



UNSHIELDED

PLUG WILL APPEAR SIMILAR TO THIS VIEW

100	6-569278-3	MP-5EU-1
500	6-569278-2	MP-5EU-5
PACKAGE	MATERIAL	CATALOG NUMBER
UNSHIELDED CATALOG NUMBER VERSIONS		