



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Olson, Joseph R	<b>Contact Title</b>	Prod Sustaining Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-24	<b>Contact Email</b>	jrolson@te.com				
<b>Contact Phone Number</b>	1-717-592-4423								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-104118-1	<b>Amount</b>	1462.088792	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	50 SYS 50 HDR DRRRA UNSHRD SN	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	50 SYSTEM 50 HDR HSG DR UNSHRD				1.0	499.548192	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	499.548192	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	14.98645	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	334.69729	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	149.86446	mg	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				25.0	15.667027	mg	
Material	2	Gold Plate				25.0	0.2065	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.20588	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	6.195E-4	mg	
Material	2	Brass				25.0	15.123127	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	25.0	0.01512313	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	25.0	9.6788	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	25.0	0.00756156	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	1.5123E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	25.0	0.00151231	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.01512313	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	25.0	0.01512313	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	25.0	5.32463	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.00151231	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.00151231	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	25.0	0.00756156	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	25.0	0.04536938	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	25.0	0.00151231	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	7.561564E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.00756156	mg	

Material	2	Nickel Plate				25.0	0.2628	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	5.256E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	2.628E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	0.26201	mg	
Material	2	Tin Plate				25.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	25.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	25.0	0.07452547	mg	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				25.0	22.834597	mg	
Material	2	Gold Plate				25.0	0.3183	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.31735	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	9.549E-4	mg	
Material	2	Brass				25.0	22.036497	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	25.0	0.0220365	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	25.0	14.10336	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	25.0	0.01101825	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	2.2037E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	25.0	0.00220365	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.0220365	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	25.0	0.0220365	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	25.0	7.75872	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.00220365	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.00220365	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	25.0	0.01101825	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	25.0	0.06610949	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	25.0	0.00220365	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	1.1018E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.01101825	mg	
Material	2	Nickel Plate				25.0	0.4052	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	8.104E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	4.052E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	0.40398	mg	
Material	2	Tin Plate				25.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	25.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	25.0	0.07452547	mg	