



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-09-08	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	2-1734839-2	<b>Amount</b>	333.05072	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	FPC CONN. 0.5MM PITCH T/C,22P	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	HOUSING				1.0	109.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	35.97	mg	
Substance	2	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	67.0	1.0	73.03	mg	
Material	1	CONTACT/HOLD DOWN - NICKEL PLATING				1.0	0.0055	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.9	1.0	0.0054945	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.0E-5	mg	
Material	1	CONTACT				1.0	129.0	mg	
Substance	2	Copper	Supplier	7440-50-8	94.15	1.0	121.4535	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.2	1.0	0.258	mg	
Substance	2	Tin	Supplier	7440-31-5	5.55	1.0	7.1595	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.1	1.0	0.129	mg	
Material	1	ACTUATOR				1.0	72.0	mg	
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	2.0	1.0	1.44	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	32.4	mg	
Substance	2	Fatty acids, C18-unsatd., dimers, polymers with ethylenediamine, hexamethylene diamine and propionic acid	Supplier	67989-30-4	53.0	1.0	38.16	mg	
Material	1	HOLD DOWN - TinPlating				1.0	0.0419	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9001	1.0	0.04185814	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	4.18581E-5	mg	

Material	1	CONTACT-GOLD PLATING				1.0	0.00332	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.00331004	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	1.0E-5	mg	
Material	1	HOLD DOWN				1.0	23.0	mg	
Substance	2	Tin	Supplier	7440-31-5	5.35	1.0	1.2305	mg	
Substance	2	Copper	Supplier	7440-50-8	94.45	1.0	21.7235	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.2	1.0	0.046	mg	