



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Olson, Joseph R	<b>Contact Title</b>	Prod Sustaining Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-24	<b>Contact Email</b>	jrolson@te.com				
<b>Contact Phone Number</b>	1-717-592-4423								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-104178-6	<b>Amount</b>	1042.0582	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	10 SYS 50 HDR SRST UNSHRD SN	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Polyester Compound				1.0	925.0	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	925.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	27.75	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	619.75	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	277.5	mg	
Sub-Item	1	SYSTEM 50 POST PLTD SN				10.0	11.70582	mg	
Material	2	Gold Plate				10.0	0.1721	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.17158	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	5.163E-4	mg	
Material	2	Tin Plate				10.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.07452547	mg	
Material	2	Gold Plate				10.0	0.00587	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	1.761E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.00585239	mg	
Material	2	Brass				10.0	11.23425	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	10.0	0.01123425	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	10.0	7.18992	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	10.0	0.00561712	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	1.1234E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	10.0	0.00112342	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.01123425	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	10.0	0.01123425	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	10.0	3.95541	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.00112342	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.00112342	mg	

Substance	3	Aluminum	Supplier	7429-90-5	0.05	10.0	0.00561712	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	10.0	0.03370275	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.00112342	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	5.617125E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.00561712	mg	
Material	2	Nickel Plate				10.0	0.219	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	4.38E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	2.19E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.21834	mg	