



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Olson, Joseph R	<b>Contact Title</b>	Prod Sustaining Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-25	<b>Contact Email</b>	jrolson@te.com				
<b>Contact Phone Number</b>	1-717-592-4423								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-104477-7	<b>Amount</b>	5983.6132	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	100 SYSTEM 50 HDR DRRR SHRD SN	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				50.0	14.989613	mg	
Material	2	Gold Plate				50.0	0.0103	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.0102691	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	3.09E-5	mg	
Material	2	Tin Plate				50.0	0.1973	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	50.0	1.971E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	50.0	0.1971	mg	
Material	2	Nickel Plate				50.0	0.4599	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	9.198E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	4.599E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.45852	mg	
Material	2	Gold Plate				50.0	0.03527	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	1.0581E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.03516419	mg	
Material	2	Brass				50.0	14.286843	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	50.0	0.01428684	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	50.0	9.14358	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	50.0	0.00714342	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	1.4287E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	0.00142868	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.01428684	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	50.0	0.01428684	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	50.0	5.03018	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.00142868	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	50.0	0.00142868	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	50.0	0.00714342	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	50.0	0.04286053	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	0.00142868	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	7.143422E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	0.00714342	mg	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				50.0	20.357231	mg	
Material	2	Gold Plate				50.0	0.0103	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.0102691	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	3.09E-5	mg	
Material	2	Tin Plate				50.0	0.1973	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	50.0	1.971E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	50.0	0.1971	mg	
Material	2	Nickel Plate				50.0	0.4599	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	9.198E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	4.599E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.45852	mg	
Material	2	Gold Plate				50.0	0.0352	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	1.056E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.0350944	mg	
Material	2	Brass				50.0	19.654531	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	50.0	0.01965453	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	50.0	12.5789	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	50.0	0.00982726	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	1.9655E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	0.00196545	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.01965453	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	50.0	0.01965453	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	50.0	6.92007	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.00196545	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	50.0	0.00196545	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	50.0	0.00982726	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	50.0	0.05896359	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	0.00196545	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	9.827265E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	0.00982726	mg	
Sub-Item	1	SYSTEM 50 SDR CLIP 150 SN				3.0	58.757	mg	
Material	2	Tin Plate				3.0	1.544	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	3.0	0.00154246	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	3.0	1.54246	mg	
Material	2	Nickel Plate				3.0	0.043	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	8.6E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	4.3E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.042871	mg	
Material	2	Phos Bronze				3.0	57.17	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	3.0	54.13056	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	0.011434	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	3.0	0.005717	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	3.0	2.57265	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	3.0	0.0085755	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	3.0	0.05717	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.005717	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	5.717E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	3.0	0.17151	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	3.0	0.05717	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.05717	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.005717	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.028585	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	3.0	0.05717	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.8585E-4	mg	
Sub-Item	1	100 SYSTEM 50 HDR HSG DR LATCH				1.0	4040.0	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	4040.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	121.2	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	2706.8	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1212.0	mg	