



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer David W	<b>Contact Title</b>	Product Compliance Engineer for DND		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-10-15	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5406721-2	<b>Amount</b>	1415.9508	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	MJ,RJ45,SM,TG RAY,13"REEL	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	BOARD LOCK,INVERTED M/JK				2.0	39.085	mg	
Material	2	Phos Bronze				2.0	37.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.037	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0037	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	2.0	0.074	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.00185	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	2.0	33.31795	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0074	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	0.1295	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	3.7E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.037	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0037	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	2.0	3.33	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.037	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.85E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00185	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0185	mg	
Material	2	Nickel Plate				2.0	0.681	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001362	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.81E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.67896	mg	
Material	2	Tin Plate				2.0	1.404	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	2.0	0.0014026	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	2.0	1.4026	mg	
Sub-Item	1	HSG,1X1,8POS,SMT,M/JK,G RAY				1.0	1197.0	mg	
Material	2	SPS-GF30				1.0	1197.0	mg	
Substance	3	1-Octene, polymer with ethene	Supplier	26221-73-8	4.5	1.0	53.865	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	9.0	1.0	107.73	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.3	1.0	63.441	mg	
Substance	3	Benzene, ethenyl-, homopolymer, syndiotactic	Supplier	28325-75-9	49.55	1.0	593.1135	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	359.1	mg	
Substance	3	Benzene, ethenyl-	Supplier	100-42-5	0.05	1.0	0.5985	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	1.6	1.0	19.152	mg	
Sub-Item	1	TERMINAL, SM T, MOD JK, PLATED				8.0	17.5976	mg	
Material	2	Phos Bronze				8.0	17.5	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	8.0	0.0175	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	8.0	0.00175	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	8.0	0.035	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	8.0	8.75E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	8.0	15.75849	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	8.0	0.0035	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	8.0	0.06125	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	8.0	1.75E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	8.0	0.0175	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	8.0	0.00175	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	8.0	1.575	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	8.0	0.0175	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	8.0	8.75E-5	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	8.0	8.75E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	8.0	0.00875	mg	
Material	2	Gold Plate				8.0	0.01	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	8.0	0.0099	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	8.0	1.0E-4	mg	
Material	2	Tin Plate				8.0	0.0876	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	8.0	8.75124E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	8.0	0.08751249	mg	