



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com				
Contact Phone Number	1-717-592-4423								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-147377-3	Amount	2016.7269072	Version	-	Identity			
Manufacturer Item Name	30 SYS50 SMT HDR DR SHD SN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Aluminum Alloy				1.0	91.3	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.1	1.0	0.0913	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.05	1.0	0.04565	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.35	1.0	0.31955	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.05	1.0	0.04565	mg	
Substance	2	Iron	Supplier	7439-89-6	0.4	1.0	0.3652	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.25	1.0	0.22825	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.05	1.0	0.04565	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.05	1.0	0.04565	mg	
Substance	2	Aluminum	Supplier	7429-90-5	95.5945	1.0	87.27778	mg	
Substance	2	Copper	Supplier	7440-50-8	0.1	1.0	0.0913	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.1	1.0	0.0913	mg	
Substance	2	Magnesium	Supplier	7439-95-4	2.8	1.0	2.5564	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	0.04565	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.565E-4	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.04565	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.004565	mg	
Material	1	Gold Plate				1.0	1.806	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	1.80058	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.005418	mg	
Material	1	Nickel Plate				1.0	4.11	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00822	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00411	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	4.09767	mg	
Material	1	Gold Plate				1.0	0.0729072	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	2.1872E-4	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.07268848	mg	
Material	1	Tin Plate				1.0	2.238	mg	

Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00223576	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9001	1.0	2.23576	mg	
Material	1	LIQUID CRYSTAL PLOYMER				1.0	1220.0	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	36.6	mg	
Substance	2	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	817.4	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	366.0	mg	
Material	1	Brass				1.0	697.2	mg	
Substance	2	Tin	Supplier	7440-31-5	0.1	1.0	0.6972	mg	
Substance	2	Copper	Supplier	7440-50-8	64.0	1.0	446.208	mg	
Substance	2	Iron	Supplier	7439-89-6	0.05	1.0	0.3486	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.006972	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.06972	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.6972	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.1	1.0	0.6972	mg	
Substance	2	Zinc	Supplier	7440-66-6	35.2085	1.0	245.47366	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.06972	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.01	1.0	0.06972	mg	
Substance	2	Aluminum	Supplier	7429-90-5	0.05	1.0	0.3486	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.3	1.0	2.0916	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.06972	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.003486	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.3486	mg	