



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com																													
Contact Phone Number		1-717-592-4423																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	6-103916-1	Amount	827.90744407	Version	-	Identity																												
Manufacturer Item Name	40 sys 50 hdr drst unshrd sn	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	40 SYSTEM 50 HDR HSG DR UNSHRD				1.0	359.674644	mg																										
Material	2	LIQUID CRYSTAL PLOYMER				1.0	359.674644	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	10.79024	mg																										
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	240.98201	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	107.90239	mg																										
Sub-Item	1	SYSTEM 50 POST PLTD SN				40.0	11.70582	mg																										
Material	2	Tin Plate				40.0	0.0746	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	40.0	7.45254E-5	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	40.0	0.07452547	mg																										
Material	2	Gold Plate				40.0	0.00587	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	1.761E-5	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.00585239	mg																										
Material	2	Brass				40.0	11.23425	mg																										
Substance	3	Tin	Supplier	7440-31-5	0.1	40.0	0.01123425	mg																										
Substance	3	Copper	Supplier	7440-50-8	64.0	40.0	7.18992	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	40.0	0.00561712	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	1.1234E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	40.0	0.00112342	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.01123425	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.1	40.0	0.01123425	mg																										
Substance	3	Zinc	Supplier	7440-66-6	35.2085	40.0	3.95541	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.00112342	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	0.00112342	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.05	40.0	0.00561712	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.3	40.0	0.03370275	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	0.00112342	mg																										

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	5.617125E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.00561712	mg	
Material	2	Gold Plate				40.0	0.1721	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.17158	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	40.0	5.163E-4	mg	
Material	2	Nickel Plate				40.0	0.219	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	4.38E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	2.19E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.21834	mg	