



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2015-09-25	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	6-104069-0	Amount	1121.638409	Version	-	Identity			
Manufacturer Item Name	14 sys 50 hdr drra shrd sn	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				7.0	13.370478	mg	
Material	2	Brass				7.0	12.631422	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	7.0	0.01263142	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	7.0	8.08411	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	7.0	0.00631571	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	7.0	1.2631E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	7.0	0.00126314	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	7.0	0.01263142	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	7.0	0.01263142	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	7.0	4.44733	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	7.0	0.00126314	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	7.0	0.00126314	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	7.0	0.00631571	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	7.0	0.03789427	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	7.0	0.00126314	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	7.0	6.315711E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	7.0	0.00631571	mg	
Material	2	Gold Plate				7.0	0.13887	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	7.0	4.1661E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	7.0	0.13845	mg	
Material	2	Nickel Plate				7.0	0.379923	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	7.0	7.5985E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	7.0	3.7992E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	7.0	0.37878	mg	
Material	2	Tin Plate				7.0	0.209943	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	7.0	2.0973E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	7.0	0.20973	mg	
Material	2	Gold Plate				7.0	0.01032	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	7.0	0.01028904	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	7.0	3.096E-5	mg	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				7.0	13.994009	mg	
Material	2	Brass				7.0	13.8282	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	7.0	0.0138282	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	7.0	8.85005	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	7.0	0.0069141	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	7.0	1.3828E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	7.0	0.00138282	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	7.0	0.0138282	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	7.0	0.0138282	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	7.0	4.8687	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	7.0	0.00138282	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	7.0	0.00138282	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	7.0	0.0069141	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	7.0	0.0414846	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	7.0	0.00138282	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	7.0	6.9141E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	7.0	0.0069141	mg	
Material	2	Gold Plate				7.0	0.00587	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	7.0	1.761E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	7.0	0.00585239	mg	
Material	2	Nickel Plate				7.0	0.006619	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	7.0	1.3238E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	7.0	1.0E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	7.0	0.00659914	mg	
Material	2	Tin Plate				7.0	0.143	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	7.0	1.4286E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	7.0	0.14286	mg	
Material	2	Gold Plate				7.0	0.01032	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	7.0	0.01028904	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	7.0	3.096E-5	mg	
Sub-Item	1	SYSTEM 50 SDR CLIP 150 SN				1.0	71.087	mg	
Material	2	Phos Bronze				1.0	64.74	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	61.2981	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.012948	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.006474	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	2.9133	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.009711	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.06474	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.006474	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	6.474E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.19422	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.06474	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.06474	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.006474	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.03237	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.06474	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.237E-4	mg	
Material	2	Nickel Plate				1.0	1.993	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.003986	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.001993	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.98702	mg	
Material	2	Tin Plate				1.0	4.354	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00434965	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	4.34965	mg	
Sub-Item	1	14 SYSTEM 50 HDR HSG DR LATCH				1.0	859.0	mg	
Material	2	LCP-GF30				1.0	859.0	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	1.718	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	25.77	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	17.18	mg	
Substance	3	2,6-Naphthalenedi carboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,4-benzenediol, [1,1'-biphenyl]-4,4'-diol and 4-hydroxybenzoic acid	Supplier	126710-21-2	65.8	1.0	565.222	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	249.11	mg	