



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china		
Company Unique ID	TE Connectivity	Response Date	2015-11-16	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-353293-6	Amount	783.2	Version	-	Identity			
Manufacturer Item Name	MINI CT MT REC ASSY 16P GRAY	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MINI CT MT REC HSG 16P GRAY				1.0	368.0	mg	
Material	2	PA66-GF20-FR				1.0	368.0	mg	
Substance	3	Phenol, 2,4(or 2,6)-dibromo-, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	69882-11-7	20.0	1.0	73.6	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	52.0	1.0	191.36	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	73.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	3.68	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	25.76	mg	
Sub-Item	1	MT REC CONT FOR 1.5 MINI CT				16.0	25.95	mg	
Material	2	Phos Bronze				16.0	24.95	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	16.0	23.62728	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	16.0	0.00499	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	16.0	0.002495	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	16.0	1.12275	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	16.0	0.0012475	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	16.0	0.02495	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	16.0	0.002495	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	16.0	2.495E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	16.0	0.07485	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	16.0	0.02495	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	16.0	0.02495	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	16.0	0.0012475	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	16.0	0.012475	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	16.0	0.02495	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	16.0	1.2475E-4	mg	
Material	2	Tin Plate				16.0	1.0	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	16.0	0.0035	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.2	16.0	0.0020	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	16.0	0.015	mg	
Substance	3	Tin	Supplier	7440-31-5	97.85	16.0	0.9785	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	16.0	0.0010	mg	