



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	TE Connectivity	Response Date	2016-01-18	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1623208-1	Amount	4.741714	Version	-	Identity																												
Manufacturer Item Name	CRG0805 1% 390R	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)																																	
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Termination inner C2				1.0	0.038975	mg																										
Substance	2	Silver	Supplier	7440-22-4	95.0	1.0	0.03702625	mg																										
Substance	2	Frits, chemicals	Supplier	65997-18-4	5.0	1.0	0.00194875	mg																										
Material	1	Substrate				1.0	4.17964	mg																										
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	100.0	1.0	4.17964	mg																										
Material	1	Protective coating G2				1.0	0.069624	mg																										
Substance	2	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane	Supplier	25068-38-6	48.0	1.0	0.03341952	mg																										
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	5.34	1.0	0.00371792	mg																										
Substance	2	C.I. Pigment Black 28	Supplier	68186-91-4	13.33	1.0	0.00928088	mg																										
Substance	2	Silica, vitreous	Supplier	60676-86-0	33.33	1.0	0.02320568	mg																										
Material	1	Termination inner C3				1.0	0.0258	mg																										
Substance	2	Nickel	Nickel	7440-02-0	80.0	1.0	0.02064	mg																										
Substance	2	Chromium	Supplier	7440-47-3	20.0	1.0	0.00516	mg																										
Material	1	Termination outer				1.0	0.14783	mg																										
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.14783	mg																										
Material	1	Termination between				1.0	0.15019	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.15019	mg																										
Material	1	Termination inner C1				1.0	0.059025	mg																										
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.059025	mg																										
Material	1	Resistive element				1.0	0.027	mg																										
Substance	2	Frits, chemicals	Supplier	65997-18-4	57.29	1.0	0.0154683	mg																										
Substance	2	Silver	Supplier	7440-22-4	35.0	1.0	0.00945	mg																										
Substance	2	Ruthenium oxide (RuO2)	Supplier	12036-10-1	5.0	1.0	0.00135	mg																										

Substance	2	Lead	Lead/Lead Compounds	7439-92-1	2.71	1.0	7.317E-4	mg	7(c)-I Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound
Material	1	Marking				1.0	0.00436	mg	
Substance	2	Oxirane, 2,2-[(1-methylethylidene)bis(4,1-phenyleneoxy)methylene]]bis-, homopolymer	Supplier	25085-99-8	52.63	1.0	0.00229467	mg	
Substance	2	Sulfuric acid, barium salt (1:1)	Supplier	7727-43-7	15.79	1.0	6.8844E-4	mg	
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	31.58	1.0	0.00137689	mg	
Material	1	Protective coating G1				1.0	0.03927	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	13.28	1.0	0.00521506	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	0.78	1.0	3.0631E-4	mg	
Substance	2	Silicon oxide	Supplier	11126-22-0	28.13	1.0	0.01104665	mg	
Substance	2	Chromium oxide (Cr2O3)	Supplier	1308-38-9	4.69	1.0	0.00184176	mg	
Substance	2	Bismuth oxide (Bi2O3)	Supplier	1304-76-3	53.12	1.0	0.02086022	mg	