



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Environmental Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2015-10-12	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	36157	Amount	1101.42153	Version	-	Identity			
Manufacturer Item Name	TERMINAL,PID G R 16-14 6	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SLEEVE ASSEMBLY 16-14				1.0	407.096	mg	
Material	2	Tin Plate				1.0	7.429	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	7.39186	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.029716	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.007429	mg	
Material	2	COLORANT				1.0	2.13024	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.32	1.0	0.00681677	mg	
Substance	3	3H-Naphtho[1,2,3-de]quinoline-2,7-dione, 3-methyl-6-[(4-methylphenyl)amino]-	Supplier	81-39-0	0.1	1.0	0.00213024	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediybis-	Supplier	110-30-5	0.0090	1.0	1.9172E-4	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediylo)imino-1,6-hexanediylo]	Supplier	32131-17-2	98.98	1.0	2.10851	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.0010	1.0	2.13024E-5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.17	1.0	0.00362141	mg	

Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-,kappa.N29,kappa.N30,kappa.N31,kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.42	1.0	0.00894701	mg	
Material	2	PA66				1.0	104.38176	mg	
Substance	3	Phosphoric acid	Supplier	7664-38-2	0.075	1.0	0.07828632	mg	
Substance	3	Acetic acid	Supplier	64-19-7	0.015	1.0	0.01565726	mg	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	89.39	1.0	93.30686	mg	
Substance	3	Acetic acid, copper(2) salt (2:1)	Supplier	142-71-2	0.02	1.0	0.02087635	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	10.43818	mg	
Substance	3	Potassium bromide	Supplier	7758-02-3	0.5	1.0	0.52191	mg	
Material	2	Copper				1.0	293.155	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.14658	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00293155	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	292.26821	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00293155	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0293155	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0293155	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.058631	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.29315	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.29315	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00146577	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0293155	mg	
Sub-Item	1	TERMINAL,BO DY RING 16-14 6				1.0	694.32553	mg	
Material	2	Tin Plate				1.0	7.59027	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	7.55232	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.03036108	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00759027	mg	
Material	2	Copper				1.0	686.73526	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.34337	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00686735	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	684.65789	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00686735	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.06867353	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.06867353	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.13735	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.68674	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.68674	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00343368	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.06867353	mg	