



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2016-05-13	Contact Email	jp.kuntz@te.com				
Contact Phone Number	717-986-5932								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1393217-1	Amount	6059.66	Version	-	Identity			
Manufacturer Item Name	RE030005	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	RE030005 After Assembly				1.0	6059.66	mg	
Material	2	Copper				1.0	1680.0	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0168	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.01	1.0	0.168	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.68	mg	
Substance	3	Copper	Supplier	7440-50-8	99.7625	1.0	1676.01	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.168	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.168	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0168	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0084	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.084	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.84	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.84	mg	
Material	2	Polyester Compound				1.0	617.0	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	117.23	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	28.5	1.0	175.845	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol]	Supplier	25971-63-5	34.2	1.0	211.014	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	9.5	1.0	58.615	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.8	1.0	54.296	mg	
Material	2	100-1777				1.0	254.0	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00127	mg	
Substance	3	Chromium	Supplier	7440-47-3	1.0	1.0	2.54	mg	
Substance	3	Tin	Supplier	7440-31-5	1.2	1.0	3.048	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00254	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0254	mg	

Substance	3	Titanium	Supplier	7440-32-6	0.8	1.0	2.032	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0254	mg	
Substance	3	Copper	Supplier	7440-50-8	95.6685	1.0	242.99799	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0254	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.254	mg	
Substance	3	Nickel	Nickel	7440-02-0	1.2	1.0	3.048	mg	
Material	2	Iron Strip				1.0	1805.0	mg	
Substance	3	Vanadium	Supplier	7440-62-2	0.0070	1.0	0.12635	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.15	1.0	2.7075	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1805	mg	
Substance	3	Titanium	Supplier	7440-32-6	0.0070	1.0	0.12635	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.36	1.0	6.498	mg	
Substance	3	Aluminium	Supplier	7429-90-5	0.09	1.0	1.6245	mg	
Substance	3	Copper	Supplier	7440-50-8	0.08	1.0	1.444	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.022	1.0	0.3971	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1805	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.01	1.0	0.1805	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	1.083	mg	
Substance	3	Iron	Supplier	7439-89-6	98.8885	1.0	1784.93743	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.022	1.0	0.3971	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.805	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01805	mg	
Substance	3	Nitrogen	Supplier	7727-37-9	0.0070	1.0	0.12635	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.07	1.0	1.2635	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.009025	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.805	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.09025	mg	
Material	2	POLYAMIDE 66				1.0	115.0	mg	
Substance	3	Boric acid, zinc salt	Supplier	1332-07-6	10.0	1.0	11.5	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	85.0	1.0	97.75	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	5.75	mg	
Material	2	Phos Bronze				1.0	48.2	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00482	mg	
Substance	3	Copper	Supplier	7440-50-8	91.9385	1.0	44.31436	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.00482	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.1446	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.00964	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.82E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0482	mg	
Substance	3	Tin	Supplier	7440-31-5	7.0	1.0	3.374	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.1687	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.00723	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.0482	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.41E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00241	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.0482	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0241	mg	
Material	2	VESTODUR X7212 NATURAL, A				1.0	975.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.0	1.0	58.5	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	41.0	1.0	399.75	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	8.0	1.0	78.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	438.75	mg	
Material	2	Silver Alloy				1.0	48.66	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.0010	1.0	4.866E-4	mg	
Substance	3	Silver	Supplier	7440-22-4	99.783	1.0	48.55441	mg	
Substance	3	Bismuth	Supplier	7440-69-9	0.0010	1.0	4.866E-4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.0010	1.0	4.866E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.0010	1.0	4.866E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	0.04866	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.0010	1.0	4.866E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0010	1.0	4.866E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.11	1.0	0.053526	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.0010	1.0	4.866E-4	mg	
Material	2	PBT-GF45				1.0	515.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	11.0	1.0	56.65	mg	
Substance	3	Aromatic Brominated flame retardant - ISO 1043-4 code #FR(16)	Supplier	1043-4-FR16	8.0	1.0	41.2	mg	
Substance	3	Poly(butylene terephthalate) - ISO 1043-1 Term PBT	Supplier	1043-1-PBT	35.0	1.0	180.25	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	5.15	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	231.75	mg	
Material	2	Tin Plate				1.0	1.3	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	1.29649	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0026	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	9.1E-4	mg	
Material	2	Nickel Plate				1.0	0.5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0010	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.0E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.4985	mg	