



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	DAVID BENFER	Contact Title	Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-11-18	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	2-292208-4	Amount	1.110304	Version	-	Identity																												
Manufacturer Item Name	MINI CT D/R DIP 24P V NAT	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	AMP MINI D/R HDR HSG V24P GRAY				1.0	0.646	g																										
Material	2	PA66-GF20-FR				1.0	0.646	g																										
Substance	3	Phenol, 2,4(or 2,6)-dibromo-, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	69882-11-7	20.0	1.0	0.1292	g																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	52.0	1.0	0.33592	g																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	0.1292	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	0.00646	g																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	0.04522	g																										
Sub-Item	1	0.5SQ POST				12.0	0.020976	g																										
Material	2	Brass				12.0	0.0205	g																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	12.0	4.1E-5	g																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	2.05E-6	g																										
Substance	3	Zinc	Supplier	7440-66-6	35.5226	12.0	0.00728213	g																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	2.05E-5	g																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	12.0	2.05E-7	g																										
Substance	3	Iron	Supplier	7439-89-6	0.05	12.0	1.025E-5	g																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	12.0	1.025E-5	g																										
Substance	3	Copper	Supplier	7440-50-8	64.0	12.0	0.01312	g																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	2.05E-7	g																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	12.0	2.0295E-6	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	1.025E-5	g																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	1.025E-7	g																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	12.0	1.025E-6	g																										
Material	2	Nickel Plate				12.0	2.34E-4	g																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.68E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	2.34E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	2.333E-4	g	
Material	2	Tin Plate				12.0	2.42E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.84E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	12.0	2.4135E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	12.0	1.694E-7	g	
Sub-Item	1	0.5SQ POST				12.0	0.017716	g	
Material	2	Brass				12.0	0.0173	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	12.0	3.46E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	1.73E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	35.5226	12.0	0.00614541	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	1.73E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	12.0	1.73E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	12.0	8.65E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	12.0	8.65E-6	g	
Substance	3	Copper	Supplier	7440-50-8	64.0	12.0	0.011072	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	1.73E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	12.0	1.7127E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	8.65E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	8.65E-8	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	12.0	8.65E-7	g	
Material	2	Nickel Plate				12.0	2.05E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.1E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	2.05E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	2.0438E-4	g	
Material	2	Tin Plate				12.0	2.11E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.22E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	12.0	2.1043E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	12.0	1.477E-7	g	