



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	TE Connectivity	Response Date	2016-05-18	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	2-640456-0	Amount	1948.8	Version	-	Identity																												
Manufacturer Item Name	20P MTA100 HDR ASSY F/L SQ STR	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	Polyester Compound				1.0	1017.9	mg																										
Material	2	PBT				1.0	1017.9	mg																										
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	2.0358	mg																										
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	50.895	mg																										
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	1.0179	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	81.432	mg																										
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	1.0179	mg																										
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	5.0895	mg																										
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	1.0179	mg																										
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	5.0895	mg																										

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	305.37	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	50.895	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	20.358	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	1.0179	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	492.6636	mg	
Sub-Item	1	100364 H03 .025IN*.025IN F				10.7	87.0	mg	
Material	2	Tin Plate				10.7	0.4785	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.7	9.57E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	10.7	0.47721	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.7	3.3495E-4	mg	
Material	2	Nickel Plate				10.7	0.3915	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.7	7.83E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.7	3.915E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.7	0.39033	mg	
Material	2	Brass Wire				10.7	86.13	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	10.7	61.58295	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.7	8.613E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	10.7	24.13587	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	10.7	0.043065	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	10.7	8.613E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	10.7	0.043065	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.7	0.08613	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	10.7	0.00852687	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.7	0.008613	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.7	0.043065	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	10.7	0.0043065	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.7	4.3065E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	10.7	0.17226	mg	