



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Environmental Engineering, Ind Central Eng																											
Company Unique ID	TE Connectivity	Response Date	2015-11-16	Contact Email	jrpenica@te.com																													
Contact Phone Number		1-717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	207604-1	Amount	12768.6	Version	-	Identity																												
Manufacturer Item Name	METRIMATE,ST R REL KIT,36P	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Manufacturing Information																																		
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info																												
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow																												
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0																											
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC																											
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC																											
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC																											
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	STRAIN RELIEF HSG,36P				2.0	6044.9	mg																										
Material	2	PA6/66-FR(22)				2.0	6044.9	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.5	2.0	90.6735	mg																										
Substance	3	Iron oxide (Fe2O3)	Supplier	1309-37-1	5.0	2.0	302.245	mg																										
Substance	3	Aliphatic/Alicyclic Chlorinated and Brominated flame retardant - ISO 1043-4 code #FR(22)	Supplier	1043-4-FR22	20.0	2.0	1208.98	mg																										
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	73.5	2.0	4443.0015	mg																										
Sub-Item	1	CABLE GATES				1.0	678.8	mg																										
Material	2	PA6/66-FR(22)				1.0	678.8	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.5	1.0	10.182	mg																										
Substance	3	Iron oxide (Fe2O3)	Supplier	1309-37-1	5.0	1.0	33.94	mg																										

Substance	3	Aliphatic/Alicyclic Chlorinated and Brominated flame retardant - ISO 1043-4 code #FR(22)	Supplier	1043-4-FR22	20.0	1.0	135.76	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	73.5	1.0	498.918	mg	