



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2016-05-19	Contact Email	jp.kuntz@te.com																													
Contact Phone Number		717-986-5932																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	208487-1	Amount	45673.472	Version	-	Identity																												
Manufacturer Item Name	CMC RECEPTACLE ASSY,SIZE 22	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	17-14 CPC REC FREE HANGING				1.0	13585.0	mg																										
Material	2	PA66-GF25-FR(52)				1.0	13585.0	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	65.5	1.0	8898.175	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	3396.25	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	271.7	mg																										
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	135.85	mg																										
Substance	3	Inorganic Red Phosphorus flame retardant - ISO 1043-4 code #FR(52)	Supplier	1043-4-FR52	6.5	1.0	883.025	mg																										
Sub-Item	1	CMC GROOVED PIN, SOLID				2.0	98.916	mg																										
Material	2	Carbon Steel				2.0	98.9	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	9.89E-4	mg																										
Substance	3	Carbon	Supplier	7440-44-0	0.18	2.0	0.17802	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	9.89E-4	mg																										
Substance	3	Iron	Supplier	7439-89-6	98.7026	2.0	97.61687	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	2.0	0.0097911	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.7	2.0	0.6923	mg																										
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	0.04945	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.03956	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.00989	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.1	2.0	0.0989	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.0989	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.04945	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.04945	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.004945	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	4.945E-4	mg																										
Material	2	Nickel Plate				2.0	0.016	mg																										

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	1.6E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.015952	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	3.2E-5	mg	
Sub-Item	1	RECEPT SHELL,SZ 22,CMC				1.0	31890.64	mg	
Material	2	Zinc Alloy				1.0	30527.4	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	10.68459	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	6.10548	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0030	1.0	0.91582	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.06	1.0	18.31644	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	76.3185	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	3.05274	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.0315	1.0	29010.64613	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	1312.6782	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	3.05274	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.30527	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	30.5274	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	30.5274	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	15.2637	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	6.10548	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0050	1.0	1.52637	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.15264	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0040	1.0	1.2211	mg	
Material	2	Nickel Plate				1.0	413.94	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.41394	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	412.69818	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.82788	mg	
Material	2	Copper Plate				1.0	949.3	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.9493	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	948.3507	mg	